

XAPG49504

die-cast empty control station - XAP-G - Ø22 - 4 cut-outs



Main

| | |
|-----------------------------|---|
| Range of product | Harmony XAP |
| Product or component type | Die-cast empty control station |
| Device short name | XAPG |
| Product destination | For Ø 22 mm control and signalling units |
| Number of cut-out | 4 cut-outs |
| Colour of base of enclosure | Grey RAL 7032 |
| Colour of cover | Grey RAL 7032 |
| Material | Zinc alloy |
| Cable entry | 1 hole with blanking plug for cable gland with <= 14 mm 1 hole without blanking plug for cable gland with <= 14 mm |
| Product mounting | Flush mounting |
| IP degree of protection | IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010 |

Complementary

| | |
|-------------------------|---|
| Number of vertical rows | 1 |
|-------------------------|---|

Environment

| | |
|---------------------------------------|--|
| protective treatment | TC |
| ambient air temperature for storage | -40...70 °C |
| ambient air temperature for operation | -25...70 °C |
| electrical shock protection class | Class I conforming to IEC 60536 Class I conforming to NF C 20-030 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.