

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0906351101

Status:

Active

Overview:

QF-50™

Description:

1.27mm Pitch QF-50 Single Beam, Vertical MIL/DIN Version, 0.10µm Gold (Au), 10 Circuits

Documents:

3D Model


Drawing (PDF)

Product Specification PS-99020-0015-001 (PDF)

Packaging Specification PK-90635-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Ribbon Cable / Wire Trap Connectors
Series	90635
Comments	Preloaded Upper Housing, Preloaded Upper Housing
Component Type	Housing
Glow-Wire Capable	No
Overview	QF-50™
Product Name	QF-50
UPC	800753657922
Physical	
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	300
Entry Angle	90° Angle
Flammability	94V-0
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	1.303/g
Number of Rows	2
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.102µm
Plating min - Termination	0.991µm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-25° to +85°C
Termination Interface: Style	IDT or Pierce
Wire Insulation Diameter	1.14mm max.
Wire Size AWG	26, 28
Wire/Cable Type	Ribbon Cable
Electrical	
Current - Maximum per Contact	1.0A



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/88/2018 (15	
January 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90635 Series

Mates With

90663

Use With

90170

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Changehead for	690080250
Parallel Action	
Handtool	690080949
Arbor Press Fixture	690200680
Semi-Automatic	691271150
Bench Press	
PB15 C/W Cable	

Voltage - Maximum	250V AC/DC	Sensor for 90635 Connectors
Material Info		
Reference - Drawing Numbers		
Packaging Specification	PK-90635-001-001	
Product Specification	PS-99020-0015-001	
Sales Drawing	SDA-90635	

This document was generated on 04/02/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION