

ECI motor.

ECI-63.XX-K4




- Drive with completely integrated 4Q operation and control electronics
- Speed, torque or position mode possible
- Selection of operating modes and parameter setting via RS485
- Extensive interface with various inputs and outputs
- Output stage enabled via digital input
- Integrated brake chopper
- Speed set values from n=0 with holding torque up to 5 000 rpm
- Excellent control behavior via field-oriented control with sine commutation
- High efficiency and high power density realized in a compact design
- User-friendly parameter setting with “Kickstart” PC software

Nominal data						
Type		ECI-63.20-K4 -B00	ECI-63.20-K4 -D00	ECI-63.40-K4 -B00	ECI-63.40-K4 -D00	ECI-63.60-K4 -D00
Nominal voltage (U_n)	V DC	24	48	24	48	48
Permissible supply voltage range (U_{zK})	V DC	18 ... 30	18 ... 53	18 ... 30	18 ... 53	18 ... 53
Max. reverse voltage	V DC	35	58	35	58	58
Nominal speed (n_n)**	rpm			4 000		
Nominal torque (M_n)**	mNm	425	450	600	750	850
Nominal current (I_n)**	A	8.50	5.40	12.3	7.20	8.60
Nominal output power (P_n)**	W	178	188	251	314	356
Starting torque (M_{max})	mNm	1 480	1 890	1 500	3 000	2 550
Speed at no-load operation (n_0)	rpm	5 800	5 800	5 900	5 800	6 000
No-load current (I_0)	A	0.50	0.50	0.90	0.50	0.60
Recommended speed control range	rpm			0 ... 5 000		
Set value input				analog / PWM / frequency / digital		
Rotor moment of inertia (J_r)	$\text{kgm}^2 \times 10^{-6}$	19	19	38	38	57
Function for motor protection at stall				thermal		
Overload protection				integrated		
Permissible ambient temperature range (T_a)	°C			0 ... +40		
Weight	kg	0.85	0.85	1.15	1.15	1.50
Order no. (wire interface)*	IP 40	932 6320 403	932 6320 405	932 6340 403	932 6340 405	932 6360 405
Order no. (connector interface)*	IP 54	932 6320 400	932 6320 402	932 6340 400	932 6340 402	932 6360 402
Subject to alterations	* Classification of protection class refers to installed state with sealing on the flange side ** At T_u max. 40°C					


Characteristic curve

ECI-63.20-K4, 24 V (at 25°C)

¹⁾ Nominal data, see table


Characteristic curve 48 V on request

ECI-63.40-K4, 24 V (at 25°C)

¹⁾ Nominal data, see table

Characteristic curve 48 V on request

ECI-63.60-K4, 48 V (at 25°C)


¹⁾ Nominal data, see table

ECI motor.


ECI-63.XX-K4

Technical drawing

All dimensions in mm




Type	L	$\varnothing D$
ECI-63.20	118.5 ± 0.3	$6_{\text{g}5}$
ECI-63.40	138.5 ± 0.3	$6_{\text{g}5}$
ECI-63.60	158.5 ± 0.3	$10_{\text{g}5}$



* For thread-rolling screws according to DIN 7500

Electrical connection





Wire color	Pin	Configuration	Function	Recommended AWG
white	1	D-IN-A	NPN 24 V	
brown	2	D-IN-B	NPN 24 V	
green	3	D-IN-1	NPN 24 V	
yellow	4	D-IN-2	NPN 24 V / analog 0 ... 10 V / brake	
gray	5	D-OUT-1	PNP 24 V	
pink	6	D-OUT-2	PNP 24 V	
blue	7	D-OUT-3*	PNP 24 V	24
red	8	A-IN-1	0 ... 10 V (differential)	
black	9	A-IN-GND	GND for analog IN 1 (differential)	
violet	10	RS485 A (+)	Progr. bus	
gray / pink	11	RS485 B (-)	Progr. bus	
red / blue	12	U_{Logic}	Logic power supply (24 V)	
gray	A	Ballast	Ballast resistor	16
brown	B	U_{ZK}	Power supply	
black	C	GND	Power / signal GND	

* Output (OUT 3) is only available on ECI-63.XX-K4

Cable

Type	Length L (mm)	Order no.
Cable (12+3 Pins)	1 000 ±30	992 0160 034
Cable (12+3 Pins)	3 000 ±30	992 0160 035

Type	Length L (mm)	Order no.
Cable (12+3 Pins)	1 000 ±30	992 0160 036
Cable (12+3 Pins)	3 000 ±30	992 0160 037



For self-assembly, cables can be obtained from Hummel:

Hummel cable connector M16 for cable Ø 8-11 mm, Tightening torque: 5 Nm (Order no. 7.810.500.000)

Hummel crimp insert series M16, socket 12+3 with special coding (Order no. 7K11886034)

Hummel crimp contact socket 3 x, power, crimp range 0.5 - 1.5 mm² (Order no. 7.010.981.202)


Hummel crimp contact socket 12 x, signal, crimp range 0.08 - 0.34 mm² (Order no. 7.010.980.802)

Modular construction kit**Brake system**


Spring-applied brake, integrated
Brake module ECI 63-K4 (p. 76)

**Basic motor****Planetary gearheads**

NoiselessPlus 63 (page 52)
Performax® 63 (page 56)
Performax®Plus 63 (page 60)
Optimax 63 (page 62)

**Commissioning tool**

"Kickstart" (page 74)

**Crown gearheads**

EtaCrown® 75 (page 66)
EtaCrown®Plus 63 (page 70)

**Cable**

Connection cables have to be ordered separately

For motor-gearbox combinations, depending on the choice of the single components, the maximum allowable torque (gearbox) can be exceeded or respectively not reached.