

This document was generated on 04/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0430450210

Status: Active

Overview: Micro-Fit 3.0 Connector System Product Family

Description: Micro-Fit 3.0 Right-Angle Header, 3.00mm Pitch, Dual Row, 2 Circuits, with Solder Tab,

Gold, Glow-Wire Capable, Black

Documents:

3D Model Drawing (PDF)

Product Specification PS-43045 (PDF)
Product Specification PS-43045-001 (PDF)

Product Specification TS-43045-001-001 (PDF)
Product Specification TS-43045-002-001 (PDF)

Product Specification TS-46235-001-001 (PDF)

Packaging Specification 430450001-PK-000 (PDF)

Packaging Specification PK-70873-05XX-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA UL

General

Product Family

Series
Application
Comments

LR19980 E29179

PCB Headers

43045


Power, Wire-to-Board
"""""High Temperature|Square Pin|Solder

Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC

60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product enduse standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."""""", """"""High Temperaturel Square Pin|Solder Type<P><P>This Molex product

Square Pin|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in

end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-



EU ELV

Not Relevant

EU RoHS Compliant

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019) Halogen-Free

Status

ELV

Low-Halogen

For more information, please visit Contact US

China ROHS

Green Image Not Relevant

China RoHS

RoHS Phthalates

Not Contained

Search Parts in this Series

43045 Series

Mates With

Micro-Fit 3.0 Receptacle Housing <u>43025</u>
br>Micro-Fit 3.0 TPA Receptacle Housing <u>172952</u> use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for

possible product options.""""""

Overview Micro-Fit 3.0 Connector System Product Family

Product Literature Order No 987650-5984
Product Name Micro-Fit 3.0
UPC 800754370004

Physical

Breakaway No Circuits (Loaded) 2 Circuits (maximum) Color - Resin Black Durability (mating cycles max) 30 Flammability 94V-0 Glow-Wire Capable Yes Mated Height 10.29mm Material - Metal **Brass** Material - Plating Mating Gold Material - Plating Termination

Material - Resin High Temperature Thermoplastic

Net Weight 0.608/g Number of Rows 2

Orientation Right Angle
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm

Packaging Type Embossed Tape on Reel

Pitch - Mating Interface 3.00mm
Plating min - Mating 0.381µm
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -40° to +105°C
Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 8.5A Voltage - Maximum 600V

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

003

Process Temperature max. C

260

Material Info

Reference - Drawing Numbers

 Packaging Specification
 430450001-PK-000, PK-70873-05XX-001

 Product Specification
 PS-43045, PS-43045-001, TS-43045-001-001,

TS-43045-002-001, TS-46235-001-001

Sales Drawing SD-43045-004-000 Symbol/Footprint Data SYM-43045-0209

This document was generated on 04/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION