



Air Ionizing Cartridge

MODEL 6110/6110A

Simco-Ion's self-contained compressed Air Ionizing Cartridge controls static charge in production, packaging, laboratory and other environments where static build-up can cause contamination, ESD, material handling problems or microprocessor lock-up. Compact and rugged, the cartridge can be used either for in-line ionization or as an ionizing blow-off gun. For in-line use, connect the 6110 to a compressed air source and it is ready to ionize any type of production equipment. Or attach the 6110 to an ordinary air gun and the airstream is ionized for effective particle removal. An internal sensor initiates ionization only when the gun is triggered, ensuring on-demand control of static charge (Model 6110A).

Features





- IsoStat® technology
- Internal air flow sensor (Model 6110A)
- Shielded emitter points
- Compact size
- Optional blow-off gun kit

Benefits



- Intrinsically balanced; no calibration needed
- On-demand ionization during gun operation
- No shock hazard
- Adapts to compressed air lines
- Fits any air gun







Specifications

Input Voltage	24 VAC, <1W from transformer
Balance	Better than $\pm 25V$ @ 6 in. (15.2 cm)
Discharge¹	$\pm 1,000$ to 100V, <4 sec;
Power Source	Wall transformer 120 VAC (powers up to 10 units); 100 VAC & 230 VAC models available
LED Indicators	Green POWER
Ion Emission	Steady state DC
Emitter Points	Tungsten alloy, estimated life 5 years of continuous use
Airflow	At least 2 scfm
Air Line	1/4 in. NPT female (input and output); 1/8 in. NPT adapter available
Internal Sensor	Turns ionizer off when air is not flowing (Model 6110A only); model without sensor also available for continuous flow applications
Dimensions	2.2D x 3.1L in. (5.6D x 7.9L cm) not including fittings
Weight	6 oz (170.1g)
Warranty	2 year limited warranty
Certifications	   

Transformer 33-1420-01

Input Voltage	120 VAC $\pm 10\%$, 60 Hz
Output Voltage	24 VAC $\pm 5\%$ @ 500 mA
Dimensions	3.0H x 1.9W x 1.6D in. (76.5 x 48.5 x 40 mm)
Weight	0.9 lb (0.4 kg)
Certifications	 

Transformer 33-1430-01 & 33-1433-01

Input Voltage	230 VAC $\pm 10\%$, 50 Hz
Output Voltage	24 VAC $\pm 5\%$ @ 500 mA
Dimensions	3.2H x 2.2W x 1.9D in. (81.5 x 56.5 x 48.5 mm)
Weight	0.9 lb (0.4 kg)
Certifications	   

1. Tested in accordance with ANSI/ESD STM3.1-2015.

Ordering Information

91-6110	Model 6110 Air Cartridge Ionizer
92-6110-US	Model 6110 Air Cartridge Ionizer & 120 VAC power supply kit
91-6110A	Model 6110A Air Cartridge Ionizer with airflow sensor
92-6110A-US	Model 6110 Air Cartridge Ionizer with air flow sensor & 120 VAC power supply kit
91-6150	Optional air gun/hose kit
33-1420-01	Power Supply Kit, 120V/24 VAC 500 mA, interconnect cable with RJ-11 6P/4C plug, US
33-1430-01	Power Supply Kit, 230V/24 VAC 500 mA, interconnect cable with RJ-11 6P/4C plug, EU
33-1433-01	Power Supply Kit, 230V/24 VAC 500 mA, interconnect cable with RJ-11 6P/4C plug, UK

IsoStat Technology

Simco-Ion's IsoStat Technology guarantees intrinsically balanced ionization and eliminates complicated feedback circuits. Ionizers incorporating this technology never need calibration and require very little maintenance. IsoStat is based on a law of physics, Conservation of Charge, which states that charge cannot be created or destroyed in an isolated system. By isolating the ionizer's emitter points from ground, IsoStat ensures equal numbers of positive and negative ions.


Applications

In-line ionization. Reduces ESD damage and microprocessor lock-up in:

- IC packaging and marking
- Surface-mount equipment
- Device testing equipment

Ionizing blow-off gun. Removes particles in:

- Printed circuit board assembly
- Medical device manufacturing
- Film processing



Optional gun/hose kit (p/n 91-6150).

SIMCO ION™
An ITW Company

DS-6110_V10 - 9/16
© 2016 Simco-Ion
All rights reserved.

Simco-Ion

Technology Group
1601 Harbor Bay Pkwy, Ste 150
Alameda, CA 94502

Tel: +1 (800) 367-2452 (in USA)
Tel: +1 (510) 217-0600

ioninfo@simco-ion.com
www.simco-ion.com