

ZCKY43

limit switch lever ZCKY - steel roller lever variable
length - -40..120 °C



Main

| | |
|----------------------------|--|
| Range of product | OsiSense XC |
| Series name | Standard format |
| Product or component type | Limit switch lever |
| Device short name | ZCKY |
| Product compatibility | XCKJ XCKL XCKM XCKS |
| Associated head | ZCKD05 ZCKE05 |
| Movement of operating head | Rotary |
| Type of operator | Roller lever spring return metal (variable length) |
| Type of approach | Lateral approach |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | Without |

Environment

| | |
|---------------------------------------|---|
| ambient air temperature for operation | -25...70 °C for standard environment 10...120 °C for high temperature -40...70 °C for low temperature |
| ambient air temperature for storage | -40...70 °C for standard environment -40...70 °C for low temperature 10...120 °C for high temperature |
| environmental characteristic | High temperature Low temperature Standard environment |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1012 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.