



Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

Complementary

Colour	Black
Material	ABS (acrylonitrile butadiene-styrene) (body) PC (polycarbonate) (terminal cover)
Product weight	0.18 kg
Marking	CE
Overvoltage category	Class II conforming to EN/IEC 61140
Mounting support	72 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	117 mA at 12 V 125 mA at 24 V 158 mA at 12 V 200 mA at 24 V
Clamping connection capacity	<= 1 x 1.5 mm ²
Width	72 mm
Height	72 mm
Depth	69.3 mm

Environment

discrete output type	NPN
signalling type	16 tones alarm
standards	EN/IEC 61000-6-2 EN/IEC 61000-6-3 UL 464
product certifications	UR
protective treatment	TC
ambient air temperature for storage	-35...70 °C
ambient air temperature for operation	-10...50 °C
IP degree of protection	IP54 (panel mounted) conforming to EN/IEC 60529
noise level	0...90 dB (continuous or intermittent tone) at 1 m

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1346 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Electronic Alarm

Dimensions

