

312-1290

MATERIAL SAFETY DATA BULLETIN

GLIS: 400311

Revision Date: 06/07/99

TRN:610865-60

MOBILGEAR 629

1. PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: MOBILGEAR 629

SUPPLIER: Mobil Oil Company Limited,
Witan Gate House,
500-600 Witan Gate,
Central Milton Keynes MK9 1ES

Health Emergency and
Customer Service Telephone: 01908-853000

Contact: Mr F. Wells

2. COMPOSITION/INFORMATION ON INGREDIENTS

CHEMICAL NAMES AND SYNONYMS: PET. HYDROCARBONS AND ADDITIVES

INGREDIENTS CONSIDERED HAZARDOUS TO HEALTH:

This product is not hazardous to health as defined by the EC
Dangerous Substances/Preparations Directives. See Section 15 for a
regulatory analysis of the ingredients.

See Section 15 for European Label Information.

3. HAZARDS IDENTIFICATION

EFFECTS OF OVEREXPOSURE: No significant effects expected.

4. FIRST AID MEASURES

EYE CONTACT: Flush thoroughly with water. If irritation occurs, call
a doctor.

SKIN CONTACT: Wash contact areas with soap and water.

INHALATION: Not expected to be a problem.

INGESTION: Not expected to be a problem. However, if greater than 1/2
litre (pint) ingested, seek medical attention.

5. FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA: Carbon dioxide, foam, dry chemical and water fog.
SPECIAL FIRE FIGHTING PROCEDURES: Water or foam may cause frothing.

Use water to keep fire exposed containers cool. Water spray may be used to flush spills away from exposures. Prevent runoff from fire control or dilution from entering waterways or drinking water supply.

SPECIAL PROTECTIVE EQUIPMENT: For fires in enclosed areas, firefighters MUST use self-contained breathing apparatus.

UNUSUAL FIRE AND EXPLOSION HAZARDS: None. Flash Point C(F): > 204(399) (IP 36 / ASTM D-92). Flammable limits - LEL NA, UEL NA.

NFPA HAZARD ID: Health: 0, Flammability: 1, Reactivity: 0

HAZARDOUS DECOMPOSITION PRODUCTS: Carbon monoxide. Elemental oxides. Metal oxides.

6. ACCIDENTAL RELEASE MEASURES

NOTIFICATION PROCEDURES: Report spills as required to appropriate authorities such as the local Environmental Health Officer or Fire Brigade. If spills are likely to enter any drain, waterway or groundwater, contact the Area Water Authority. In case of accident or road spill, contact the Police and Fire Brigade and, if appropriate, the Area Water Authority.

PROCEDURES IF MATERIAL IS RELEASED OR SPILLED: Contain and adsorb on fire retardant treated sawdust, diatomaceous earth, etc. Shovel up and dispose of at an appropriate licensed waste disposal site in accordance with current applicable laws and regulations and product characteristics at time of disposal.

ENVIRONMENTAL PRECAUTIONS: Prevent spills from entering storm sewers or drains and contact with soil.

PERSONAL PRECAUTIONS: See Section 8

7. HANDLING AND STORAGE

HANDLING: No special precautions are necessary beyond normal good hygiene practices. See Section 8 for additional personal protection advice when handling this product.

STORAGE: Do not store in open or unlabelled containers. Store away from strong oxidizing agents or combustible material.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

VENTILATION: No special requirements under ordinary conditions of use and with adequate ventilation.

RESPIRATORY PROTECTION: No special requirements under ordinary conditions of use and with adequate ventilation.

EYE PROTECTION: Normal industrial eye protection practices should be employed.

SKIN PROTECTION: No special equipment required. However, good personal hygiene practices should always be followed.

EXPOSURE LIMITS: This product does not contain any components which have recognized exposure limits. However, a product exposure limit of 5.00 mg/m³ is suggested for oil mist.

9. PHYSICAL AND CHEMICAL PROPERTIES

Typical physical properties are given below. Consult Product Data Sheet for specific details.

PHYSICAL STATE: Liquid
COLOUR: Dark Amber
ODOUR: Mild
ODOUR THRESHOLD-ppm: NE
pH: NA
BOILING POINT C(F): > 316(600)
MELTING POINT C(F): NA
FLASH POINT C(F): > 204(399) (IP 36 / ASTM D-92)
FLAMMABILITY: NE
AUTO FLAMMABILITY: NE
EXPLOSIVE PROPERTIES: NA
OXIDIZING PROPERTIES: NA
VAPOUR PRESSURE-mmHg 20 C: < 0.1
VAPOUR DENSITY: > 2.0
EVAPORATION RATE: NE
RELATIVE DENSITY, 15/4 C: 0.887
SOLUBILITY IN WATER: Negligible
PARTITION COEFFICIENT: > 3.5
VISCOSITY AT 40 C, cSt: 150.0
VISCOSITY AT 100 C, cSt: 15.8
POUR POINT C(F): -27(-17)
FREEZING POINT C(F): NE
NA=NOT APPLICABLE NE=NOT ESTABLISHED D=DECOMPOSES

FOR FURTHER TECHNICAL INFORMATION, CONTACT YOUR MARKETING REPRESENTATIVE

10. STABILITY AND REACTIVITY

STABILITY (THERMAL, LIGHT, ETC.): Stable.
CONDITIONS TO AVOID: Extreme heat.
INCOMPATIBILITY (MATERIALS TO AVOID): Strong oxidisers.
HAZARDOUS DECOMPOSITION PRODUCTS: Carbon monoxide. Elemental oxides.
Metal oxides.
HAZARDOUS POLYMERISATION: Will not occur.

11. TOXICOLOGICAL DATA

---ACUTE TOXICOLOGY---

ORAL TOXICITY: Practically non-toxic (LD50: greater than 2000 mg/kg). ---Based on testing of similar products and/or the components.

DERMAL TOXICITY: Practically non-toxic (LD50: greater than 2000 mg/kg). ---Based on testing of similar products and/or the components.

INHALATION TOXICITY: Practically non-toxic (LC50: greater than 5 mg/l). ---Based on testing of similar products and/or the components.

EYE IRRITATION: Practically non-irritating. (Draize score: 0 or greater but 6 or less). ---Based on testing of similar products and/or the components.

SKIN IRRITATION: Practically non-irritating. (Primary Irritation Index: greater than 0.5 but less than 3). ---Based on testing of similar products and/or the components.

OTHER ACUTE TOXICITY DATA: The acute toxicological results summarized above are based on testing of representative products. Representative formulations have shown no acute effects, administered via the inhalation route, when tested at maximum attainable oil mist or vapour concentrations.

---SUBCHRONIC TOXICOLOGY (SUMMARY)---

Severely solvent refined and severely hydrotreated mineral base oils have been tested at our Environmental and Health Sciences Laboratory at doses significantly higher than those expected during normal industrial exposure. Extensive evaluations showed no adverse effects.

---CHRONIC TOXICOLOGY (SUMMARY)---

The base oils in this product are severely solvent refined and/or severely hydrotreated. Chronic skin painting studies of severely treated oils showed no evidence of carcinogenic effects. These results are confirmed on a continuing basis using various screening methods such as the Modified Ames Test and IP-346.

---SENSITIZATION (SUMMARY)---

Representative formulations have not caused skin sensitization in guinea pigs.

12. ECOLOGICAL INFORMATION

ENVIRONMENTAL FATE AND EFFECTS: This product is expected to be inherently biodegradable. There is no evidence to suggest bioaccumulation will occur.

Acute LC/EC50: Juvenile Rainbow Trout: Practically non-toxic
---Based on testing of similar products.

Accidental spillage may lead to penetration in soil and groundwater. However, there is no evidence that this would cause adverse ecological effects.

13. DISPOSAL CONSIDERATIONS

WASTE DISPOSAL: Product is suitable for burning in an enclosed, controlled burner for fuel value or disposal by supervised incineration. Such burning may be limited by the controlling authority. In addition, the product is suitable for processing by an approved recycling facility or can be disposed of at any licensed waste disposal site. Use of these methods is subject to user compliance with applicable laws and regulations and consideration of product characteristics at time of disposal.

EUROPEAN WASTE CODE: 13 02 02 (non-chlorinated engine, gear and lubricating oils) Waste generated from the intended use of this product is assigned the above waste disposal code. However, deviation from the intended use and/or the presence of any potential contaminants may require an alternative waste disposal code to be assigned by the end user.

14. TRANSPORT INFORMATION

USA DOT: NOT REGULATED BY USA DOT.

RID/ADR: NOT REGULATED BY RID/ADR.

IMO: NOT REGULATED BY IMO.

IATA: NOT REGULATED BY IATA.

15. REGULATORY INFORMATION

EU Labelling: EU labelling not required.

THE FOLLOWING PRODUCT INGREDIENTS ARE CITED ON THE LISTS BELOW:

CHEMICAL NAME	CAS NUMBER	LIST CITATIONS		
*** NO REPORTABLE INGREDIENTS ***				
--- REGULATORY LISTS SEARCHED ---				
1=IARC 1	6=NO ALLERGI	11=DE TERAT B	16=DE CARC B	21=CH CARC
2=IARC 2A	7=SE ALLERGY	12=DE TERAT C	17=AT TERAT A	
3=IARC 2B	8=SE CARC	13=DE TERAT D	18=AT TERAT B	
4=NTP CARC	9=DK CARC	14=DE CARC A1	19=AT TERAT C	
5=NTP SUS	10=DE TERAT A	15=DE CARC A2	20=AT TERAT D	

CARC=CARCINOGEN; SUS=SUSPECTED CARCINOGEN; TERAT=TERATOGENIC

AT = Austria	DE = Germany	NO = Norway
CH = Switzerland	DK = Denmark	SE = Sweden

16. OTHER INFORMATION

USE: Industrial gear oil

NOTE: This product should not be used for any other purpose without expert advice.

COSHH Regulations: Product reviewed and no action under COSHH considered necessary.

NOTE: PRODUCT IS NOT FORMULATED TO CONTAIN PCBS.

Any sections of this Material Safety Data Bulletin which are printed in bold text highlights recent significant changes which have been made to the advice or information given.

For Internal Use Only: MHC: 1* 1* 0* 0* 1*, MPPEC: A, TRN:

610865-60, GLIS: 400311, CMCS97: 970874

EHS Approval Date: 22JUN1999

It is believed that all the information given in this bulletin (which supersedes all previous issues) is accurate at the time of printing. Such information is offered in good faith but without guarantee and without any representation that the product concerned is suitable for any use or application. Without limitation of the foregoing, nothing herein shall be construed as a recommendation for uses which infringe valid patents or as extending any licence under valid patents.

We pursue a policy of constant research and development aimed at product improvement and, therefore, we reserve the right to change the formulation, specification and characteristics of products without notice. User should verify current specifications with us and ascertain that products are suitable for intended uses and applications.

Where the information provided herein discloses a potential hazard or hazardous ingredient, adequate warning must be provided to employees and users and appropriate precautions taken, including the practice of good industrial hygiene.

Copyright 1996 MBRC, All rights reserved

Environmental, Health and Safety Department, Paulsboro. NJ. USA.

END OF DOCUMENT