

Product datasheet

Characteristics

XACB3191

pendant control station XAC-B - 2 pushbuttons 1
Emergency stop



Main

Range of product	Harmony XAC
Product or component type	Pendant control station
Device short name	XACB

Complementary

Control station type	Double insulated
Enclosure material	Glass reinforced polyester
Electrical circuit type	Power circuit
Enclosure type	Complete ready for use
Control station application	Control of single speed hoist motor
Control station composition	2 push-buttons + 1 emergency stop
Control button type	Stop push-button Ø 40 mm 3 NC latching First push-button 2-pole raise, slow Second push-button 2-pole lower, slow
Product compatibility	XESD1191 for reversing operation XACS499 for emergency stop
Mechanical interlocking	With mechanical interlocking
Control station colour	Yellow
Connections - terminals	Screw clamp terminals 1 x 2.5 mm ² with or without cable end Screw clamp terminals 2 x 1.5 mm ² with or without cable end
Standards	EN/IEC 60204-32 EN/IEC 60947-5-1 CSA C22.2 No 14
Product certifications	CSA type 4
Protective treatment	TH
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn 10...500 Hz IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Oversupply category	Class II IEC 61140
IP degree of protection	IP65 IEC 60529
Mechanical durability	1000000 cycles
Cable entry	Rubber sleeve with stepped entry 10...22 mm
[Ithe] conventional enclosed thermal current	12 A
[Ui] rated insulation voltage	400 V 3 IEC 60947-1 emergency stop contact 600 V CSA
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-1
Contact operation	Snap action
Operating force	17 N push-button 40 N emergency stop
Short-circuit protection	<= 10 A fuse protection cartridge aM
Rated power in hp	2 hp CSA 240 V 3 hp CSA 600 V 5 hp CSA 400 V
Rated operational power in W	2200 W AC-3 240 V IEC 60947-3 appendix A

	2200 W AC-3 400 V IEC 60947-3 appendix A 2200 W AC-4 240 V IEC 60947-3 appendix A 2200 W AC-4 400 V IEC 60947-3 appendix A
Electrical durability	300000 cycles AC-3 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-3 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4 2200 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 300000 cycles AC-4 2200 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-3 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 500000 cycles AC-4 1500 W 240 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-3 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 800000 cycles AC-4 1500 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A
Terminals description ISO n°1	(13-14)NO (23-24)NO (33-34)NO (43-44)NO
Terminals description ISO n°2	(11-12)NC (21-22)NC (31-32)NC
Terminal identifier	(11-12)NC (13-14)NO
Product weight	0.94 kg

Environment

Contractual warranty

Warranty period	18 months
-----------------	-----------