

XCSE7313

metal safety switch XCSE - 2NC+1NO - slow break-
2 entries tapped 1/2" NPT- 24V



Main

| | |
|--|---|
| Range of product | Preventa Safety detection |
| Product or component type | Safety switch |
| Component name | XCSE |
| Design | Rectangular |
| Material | Metal |
| Head type | Key operated turret head |
| Contacts type and composition | 2 NC + 1 NO |
| Contact operation | Slow-break, break before make |
| Solenoid contacts type and composition | 1 NC + 1 NO (slow-break, simultaneous) |
| Cable entry | 2 entries tapped 1/2" NPT |
| Electromagnet interlocking | Locking on de-energisation and unlocking on energisation of solenoid |
| [Us] rated supply voltage | 24 V (- 20...10 %) |
| Electrical connection | Terminal, 1 x 0.5...2 x 1.5 mm ² with or without cable end |
| Number of poles | 3 |
| Locking options description | With interlocking, locking by solenoid |
| Local signalling | 2 LEDs green or orange (guard open/guard closed and locked) |
| Signalling circuit voltage | 24/48 V (voltage limits: 20...52 V) |

Complementary

| | |
|--|--|
| Positive opening | With NC contact |
| Supply voltage type | AC/DC |
| Supply frequency | 50/60 Hz |
| Load factor | 1 |
| Power consumption in VA | 10 VA (inrush) 10 VA (sealed) |
| Signalling circuit type | AC/DC |
| Signalling circuit consumption | 7 mA |
| Mechanical durability | >= 1000000 cycles |
| Minimum actuation speed | 0.01 m/s |
| Maximum actuation speed | 0.5 m/s |
| [Ie] rated operational current | 0.55 A at 125 V utilisation category DC-13, Q300 conforming to EN/IEC 60947-5-1 0.27 A at 250 V utilisation category DC-13, Q300 conforming to EN/IEC 60947-5-1 3 A at 120 V utilisation category AC-15, B300 conforming to EN/IEC 60947-5-1 1.5 A at 240 V utilisation category AC-15, B300 conforming to EN/IEC 60947-5-1 |
| [Ithe] conventional enclosed thermal current | 6 A |
| [Ui] rated insulation voltage | 50 V for signalling circuit conforming to EN/IEC 60947-1 |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to EN/IEC 60947-5-1 |
| Protection type | Overvoltage protection for signalling circuit |
| Short-circuit protection | 10 A cartridge fuse type gG (gl) |
| Actuator forcible withdrawal rtc | 2000 N |
| Actuator force for extraction | >= 20 N |
| Operating rate | 10 cyc/mn for maximum durability |
| Safety level | Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

conforming to EN/IEC 61508

| | |
|-------------------------|--|
| Safety reliability data | B10d = 5000000 (value given for a life time of 20 years limited by mechanical or contact wear) |
| Body material | Zamak |
| Head material | Zamak |
| Depth | 44 mm |
| Height | 146 mm |
| Width | 98 mm |
| Product weight | 1.14 kg |

Environment

| | |
|---------------------------------------|--|
| standards | EN 1088/ISO 14119 EN/IEC 60204-1 EN/IEC 60947-5-1 EN/ISO 12100 UL 508 CSA C22.2 No 14 |
| product certifications | CSA UL |
| protective treatment | TC |
| ambient air temperature for operation | -25...40 °C |
| ambient air temperature for storage | -40...70 °C |
| vibration resistance | 5 gn (f = 10...500 Hz) conforming to IEC 60068-2-6 |
| shock resistance | 10 gn for 11 ms conforming to IEC 60068-2-27 |
| electrical shock protection class | Class I conforming to EN/IEC 61140 |
| IP degree of protection | IP67 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Not Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1345 - Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold |
| Product end of life instructions | Available |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|