



### Main

Range of product	OsiSense XG
Product or component type	Electronic tag
RFID electronic tag name	XGHB
RFID frequency	13.56 MHz
Design	Cylindrical M18
Memory capacity	256 B
Associated smart antenna	XGCS
[Sn] nominal sensing distance	20 mm with XGCS85 18 mm with XGCS49 20 mm with XGCS89
Outer dimension	M18 x 1 x 12
Quantity per set	Set of 5
Read time	12 + 0.825 x (number of 16-bit words) ms
Write time	19 + 4.1 x (number of 16-bit words) ms
IP degree of protection	IP68
Fixing mode	By screws

### Complementary

Memory type	EEPROM
Memory operation	Read/write
Number of read cycles	Unlimited
Number of write cycles	2500000 at 30 °C 100000 at -25...70 °C
Maximum linear speed with "auto read/write function"	With XGCS49 (read a serial number) With XGCS49 (read a word) With XGCS49 (read or write 10 words) With XGCS89 (read a serial number) With XGCS89 (read a word) With XGCS89 (read or write 10 words) With XGCS85 (read a serial number)

With XGCS85 (read a word)  
With XGCS85 (read or write 10 words)

Data retention time	10 yr
Material	PBT (polybutylene terephthalate)
Product weight	0.02 kg

## Environment

Standards	ISO 15693
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	2 mm (f = 5...29.5 Hz) conforming to EN 60068-2-6 7 gn (f = 29.5...150 Hz) conforming to EN 60068-2-6
Shock resistance	30 gn for 11 ms conforming to EN 60068-2-27
IK degree of protection	IK02 conforming to EN 50102

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0824 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty


Warranty period	18 months
-----------------	-----------

---

Dimensions


---

Updatable Code Electronic Tags



Minimum Mounting Distances

Distance Between Tags



XGCS4901201 smart antenna (format 40)		XGCS8•• smart antennas (format 80)	
e1	e2	e1	e2
40	10	120	20

---

Minimum Mounting Distances in a Metal Structure

---

No metal parts within 25 mm of the tag