




Description

A range of M-MA and PG-MA cable glands that have ultra-strong stretching resistance, water proof and dust proof. They also have the ability to resist salt, acid, alkali, grease and general solvents.

Specifications

Material : Nickel plated brass with nylon claw.
 Operating temperature : -40°C to +100°C (Static state)
 -20°C to +80°C (Dynamic state)
 IP Rating : IP68

Diagram



SL	Material
A	Nickel Plated Brass
B	Nitrile Rubber
C	Nickel Plated Brass
D	Nylon PA66
E	Nitrile Rubber
F	Nickel Plated Brass

M-MA Type Metallic Cable Glands

Part Number	Thread Size	Cable Range mm	Thread OD L2 (mm)	Thread Length L1 (mm)	Spanner Size C&F (mm)
PP002680	M12×1.5	4 - 7	12	6	14
PP002686	M12×1.5	4 - 7	12	6	14
PP002681	M16×1.5	5 - 8	16	7	18
PP002687	M16×1.5	5 - 8	16	7	18
PP002682	M20×1.5	8 - 12	20	8	22
PP002688	M20×1.5	8 - 12	20	8	22
PP002683	M25×1.5	11 - 14	25	9	27/24
PP002689	M25×1.5	11 - 14	25	9	27/24
PP002684	M32×1.5	16 - 22	32	11	34
PP002690	M32×1.5	16 - 22	32	11	34
PP002685	M40×1.5	23 - 28	40	12	45
PP002691	M40×1.5	23 - 28	40	12	45

PG-MA Type Metallic Cable Glands

Part Number	Thread Size	Cable Range mm	Thread OD L2 (mm)	Thread Length L1 (mm)	Spanner Size C&F (mm)
PP002692	PG7	4 - 7	12.5	6	14
PP002699	PG7	4 - 7	12.5	6	14
PP002693	PG9	5 - 8	15.2	7	18
PP002700	PG9	5 - 8	15.2	7	18
PP002694	PG11	6 - 10	18.6	8	20
PP002701	PG11	6 - 10	18.6	8	20
PP002695	PG13.5	8 - 12	20.4	9	22
PP002702	PG13.5	8 - 12	20.4	9	22
PP002696	PG16	11 - 14	22.5	9	24
PP002703	PG16	11 - 14	22.5	9	24
PP002697	PG21	14 - 18	28.3	9	30
PP002704	PG21	14 - 18	28.3	9	30
PP002698	PG29	18 - 25	37	10	40
PP002705	PG29	18 - 25	37	10	40

Part Number Table

Description	Part Number	Description	Part Number
Cable Gland, Brass, M12×1.5mm	PP002680	Cable Gland, Brass, PG9	PP002693
Cable Gland, Brass, M16×1.5mm	PP002681	Cable Gland, Brass, PG11	PP002694
Cable Gland, Brass, M20×1.5mm	PP002682	Cable Gland, Brass, PG13.5	PP002695
Cable Gland, Brass, M25×1.5mm	PP002683	Cable Gland, Brass, PG16	PP002696
Cable Gland, Brass, M32×1.5mm	PP002684	Cable Gland, Brass, PG21	PP002697
Cable Gland, Brass, M40×1.5mm	PP002685	Cable Gland, Brass, PG29	PP002698
Cable Gland, Brass, M12×1.5mm, 10/PK	PP002686	Cable Gland, Brass, PG7, 10/PK	PP002699
Cable Gland, Brass, M16×1.5mm, 10/PK	PP002687	Cable Gland, Brass, PG9, 10/PK	PP002700
Cable Gland, Brass, M20×1.5mm, 10/PK	PP002688	Cable Gland, Brass, PG11, 10/PK	PP002701
Cable Gland, Brass, M25×1.5mm, 10/PK	PP002689	Cable Gland, Brass, PG13.5, 10/PK	PP002702
Cable Gland, Brass, M32×1.5mm, 10/PK	PP002690	Cable Gland, Brass, PG16, 10/PK	PP002703
Cable Gland, Brass, M40×1.5mm, 5/PK	PP002691	Cable Gland, Brass, PG21, 10/PK	PP002704
Cable Gland, Brass, PG7	PP002692	Cable Gland, Brass, PG29, 10/PK	PP002705

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.