


www.vishay.com

Vishay Siliconix

Automotive N-Channel 40 V (D-S) 175 °C MOSFET



PRODUCT SUMMARY					
V _{DS} (V)	40				
$R_{DS(on)}(\Omega)$ at $V_{GS} = 10 \text{ V}$	0.00233				
I _D (A)	100				
Configuration	Single				
Package	TO-252 reverse lead DPAK				

FEATURES

- TrenchFET® power MOSFET
- Package with low thermal resistance
- Ni plated drain tab area (heatsink) for top side cooling
- 100 % R_a and UIS tested
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

280 46

105.8

107

35

-55 to +175

mJ

W

°C



o o	J			
Package	TO-252 reverse lead DPAK	N-C	hannel MOSFET S	
ABSOLUTE MAXIMUM RA	TINGS (T _C = 25 °C, unl	ess otherwise note	d)	
PARAMETER		SYMBOL	LIMIT	UNIT
Drain-source voltage		V _{DS}	40	V
Gate-source voltage	V_{GS}	± 20] v	
Continuous drain current	T _C = 25 °C	а	100	
Continuous drain current	$T_{C} = 25 ^{\circ}C$ $T_{C} = 125 ^{\circ}C$	C ID	87.5]
Continuous source current (diode con	Is	97	Α	

L = 0.1 mH

 $T_C = 25 \, ^{\circ}C$

T_C = 125 °C

THERMAL RESISTANCE RATINGS					
PARAMETER		SYMBOL	LIMIT	UNIT	
Junction-to-ambient F	PCB mount c	R_{thJA}	50	°C/W	
Junction-to-case (drain)		R_{thJC}	1.4]	

 I_{DM}

 I_{AS}

 E_{AS}

 P_{D}

T_J, T_{stg}

Notes

a. Package limited

Pulsed drain current b

Single pulse avalanche current

Single pulse avalanche energy

Maximum power dissipation b

b. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %

Operating junction and storage temperature range

c. When mounted on 1" square PCB (FR4 material)



www.vishay.com

Vishay Siliconix

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT	
Static					•	•		
Drain-source breakdown voltage	V _{DS}	V _{GS} =	= 0 V, I _D = 250 μA	40	-	-	V	
Gate-source threshold voltage	V _{GS(th)}	V _{DS} =	- V _{GS} , I _D = 250 μA	2.5	3.0	3.5	l v	
Gate-source leakage	I _{GSS}	V _{DS} =	$0 \text{ V}, \text{ V}_{GS} = \pm 20 \text{ V}$	-	-	± 100	nA	
Zero gate voltage drain current		V _{GS} = 0 V V _{DS} = 40 V		-	-	1		
	I _{DSS}	V _{GS} = 0 V	V _{DS} = 40 V, T _J = 125 °C	-	-	50	μA	
		V _{GS} = 0 V	V _{DS} = 40 V, T _J = 175 °C	-	-	500	μΑ	
On-state drain current ^a	I _{D(on)}	V _{GS} = 10 V	$V_{DS} \ge 5 \text{ V}$	50	-	-	Α	
		V _{GS} = 10 V	I _D = 20 A	-	0.00190	0.00233		
Drain-source on-state resistance ^a	R _{DS(on)}	V _{GS} = 10 V	I _D = 20 A, T _J = 125 °C	-	-	0.00390	Ω	
		V _{GS} = 10 V	I _D = 20 A, T _J = 175 °C	-	-	0.00470		
Forward transconductance b	9 _{fs}	V _{DS} = 15 V, I _D = 20 A		ı	84	-	S	
Dynamic ^b						•	L	
Input capacitance	C _{iss}		V _{DS} = 25 V, f = 1 MHz	-	5405	8000	pF	
Output capacitance	C _{oss}	$V_{GS} = 0 V$		-	1942	2700		
Reverse transfer capacitance	C _{rss}				175	250	1	
Total gate charge ^c	Qg			-	84	130		
Gate-source charge c	Q _{gs}	$V_{GS} = 10 \text{ V}$ $V_{DS} = 20 \text{ V}, I_D = 50 \text{ A}$		-	29.5	-	nC	
Gate-drain charge ^c	Q _{gd}			1	19.5	-	1	
Gate resistance	R _g	f = 1 MHz		1	2	3	Ω	
Turn-on delay time ^c	t _{d(on)}			-	17	30		
Rise time ^c	t _r	V_{DD} = 20 V, R_L = 0.4 Ω I_D \cong 50 A, V_{GEN} = 10 V, R_g = 1 Ω		-	17	30	ns	
Turn-off delay time ^c	t _{d(off)}			ı	34	60		
Fall time ^c	t _f			ı	18	35		
Source-Drain Diode Ratings and Chara	cteristics ^b					•	ı	
Pulsed current a	I _{SM}			-	-	280	Α	
Forward voltage	V _{SD}	I _F = 25 A, V _{GS} = 0 V		-	0.8	1.5	V	
Body diode reverse recovery time	t _{rr}			-	41	85	ns	
Body diode reverse recovery charge	Q _{rr}			-	28	60	nC	
Reverse recovery fall time	t _a			-	24	-		
Reverse recovery rise time	t _b			-	17	-	ns	
Body diode peak reverse recovery current	I _{RM(REC)}			-	-1.36	-	Α	


Notes


- a. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %
- b. Guaranteed by design, not subject to production testing
- c. Independent of operating temperature


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.





TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)



















TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




On-Resistance vs. Junction Temperature




On-Resistance vs. Gate-to-Source Voltage




Drain Source Breakdown vs. Junction Temperature



Source Drain Diode Forward Voltage



Threshold Voltage



Safe Operating Area


Note

a. V_{GS} > minimum V_{GS} at which $R_{DS(on)}$ is specified


For technical questions, contact: automostech



THERMAL RATINGS (T_A = 25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case


Note

- The characteristics shown in the two graphs
 - Normalized Transient Thermal Impedance Junction-to-Ambient (25 °C)
 - Normalized Transient Thermal Impedance Junction-to-Case (25 °C) are given for general guidelines only to enable the user to get a "ball park" indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?76927.

Vishay Siliconix

TO-252 Reverse Lead Case Outline



Notes

- Dimension L3 for reference only
- Area Z: unplated area more than 80 % heatsink area and for partial plating part only

DIM.	MILL	IMETERS	INCHES		
DIM.	MIN.	MAX.	MIN.	MAX.	
Α	2.23	2.33	0.088	0.092	
A1	0.64	0.89	0.025	0.035	
A2	0.03	0.18	0.001	0.007	
b	0.71	0.88	0.028	0.035	
b1	0.76	1.14	0.030	0.045	
b2	5.23	5.44	0.206	0.214	
С	0.46	0.58	0.018	0.023	
C1	0.46	0.58	0.018	0.023	
D	5.97	6.22	0.235	0.245	
D1	4.49	5.00	0.177	0.197	
E	6.48	6.73	0.255	0.265	
E1	4.32	-	0.170	-	
е	2.28 BSC		0.090 BSC		
e1	4.:	57 BSC	0	180 BSC	
Н	9.65	10.41	0.380	0.410	
L	1.40	1.78	0.055	0.070	
L1	2.74 BSC		0.	108 BSC	
L2	0.89	1.27	0.035	0.050	
L3	1.15	1.52	0.040	0.060	
M	-	1.00 (reference only)	-	0.039 (reference only	

ECN: T16-0952-Rev. D, 16-Jan-17

DWG: 5894



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.