



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	ZC2J
Product compatibility	XC2J
Associated head	ZC2JE09
Movement of operating head	Rotary
Type of operator	Stay put forked arm with rollers stay put thermoplastic (2 tracks)
Type of approach	Lateral approach

Complementary

Switch actuation	By specific cam
Positive opening	Without

Environment

Ambient air temperature for operation	-40...70 °C for low temperature -25...70 °C for standard environment
Ambient air temperature for storage	-40...70 °C for low temperature -40...70 °C for standard environment
Environmental characteristic	Low temperature Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1618 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------