



## Main

Range of product	OsiSense XU
Sensor name	XUF
[Sn] nominal sensing distance	2 m XUFZ01 0.3 m 0.3 m XUFZ02
End fitting type	M2.6 x 0.45, standard thread end fitting

## Complementary

Electronic sensor type	Photo-electric sensor
Sensor design	Fiber design
Product destination	XUDA
Optic fiber material	PMMA
Sheath material	PE
Detection system	Thru beam
Optic fiber use	Long sensing fiber
Optic fiber length	2 m
External diameter	2.2 mm
Minimum bending radius	25 mm
Thread type	M4 x 0.7
Optic fiber core	1 x Ø 1.5 mm
Product weight	0.058 kg

## Environment

Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C
Vibration resistance	+/- 1.5 mm at 10...55 Hz conforming to IEC 60068-2-6 7 gn at 10...55 Hz conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP64 conforming to IEC 60529 IP641 conforming to NF C 20-010

Offer Sustainability

---

RoHS (date code: YYWW)	Compliant - since 0648 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

---

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---