


XKBZ994

contacts block with Dead man's hdl or with built-in pushbutton hdl - for XKB



Main

Product or component type	Controllers separate parts
Accessory / separate part category	Control accessory
Product specific application	Light hoisting applications
Product compatibility	XKB
Accessory / separate part type	Contacts block
Accessory / separate part specific characteristic	For use with built-in push-button handle For use with Dead man's handle

Complementary

Contact block per direction [control circuit]	1 zero (center) position 2 zero per movement 4 per movement
Electrical connection	Screw clamp terminal, connection capacity: 1 x 0.5...1 x 1.5 mm ² Screw clamp terminal, connection capacity: 1 x 0.5...1 x 2.5 mm ²
Enclosure/cubicle description	Monobloc
Contacts type and composition	1 NO 2 NC 8 NO
Contact operation	Double-break Slow-break
[I _{th}] conventional free air thermal current	10 A conforming to IEC 337-1 10 A conforming to NF C 63-140 10 A conforming to VDE 0660 10 A conforming to CSA C22.2 No 14
[U _i] rated insulation voltage	500 V AC/DC conforming to IEC 158-1 500 V AC/DC conforming to NF C 20-040 500 V AC/DC conforming to VDE 0110
Resistance across terminals	25 mOhm at 1 A conforming to NF C 93-050
Positive opening	With
Short-circuit protection	10 A cartridge fuse type gG conforming to IEC 337-1B 10 A cartridge fuse type gG conforming to VDE 0660 part 2
Electrical durability	1000000 cycles DC inductive load at 120 V, power broken = 75 conforming to IEC 337-1 DC-11, operating rate = 60 cyc/mn 0.5 1000000 cycles DC inductive load at 24 V, power broken = 90 conforming to IEC 337-1 DC-11, operating rate = 60 cyc/mn 0.5 1000000 cycles DC inductive load at 48 V, power broken = 90 conforming to IEC 337-1 DC-11, operating rate = 60 cyc/mn 0.5
Product weight	0.215 kg

Environment

standards	CENELEC EN 50013
-----------	------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.