

PCB receptacle male back D-cod 4-pole



Part number	21 03 381 1430
Specification	PCB receptacle male back D-cod 4-pole
HARTING eCatalogue	https://b2b.harting.com/21033811430

Identification

Category	Connector
Series	Circular connectors M12
Element	PCB adapter
	Straight
Specification	incl. housing
	for rear mounting

Version

Termination method	Reflow soldering termination (THR/SMC)
Gender	Male
Locking type	Screw locking
Shielding	Shielded
Number of contacts	4
Coding	D-coding

Technical characteristics

Rated current	4 A
Rated voltage	50 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Insulation resistance	> 10 ⁸ Ω
Contact resistance	≤10 mΩ
Ambient temperature	-40 +85 °C
Mating cycles	≥100



Technical characteristics

Degree of protection acc. to IEC 60529	IP67
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Isolation group	I (600 ≤ CTI)

Material properties

Material (insert)	LCP
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
China RoHS REACH Annex XVII substances	50 No
REACH Annex XVII substances	No

Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	60
Net weight	24.5 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440402 PCB connector