



Main

Range of product	L525
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L525
Associated complete product	L525
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller pin lever length: 5.73 in belt conveyor monitoring cylindrical roller pin
Type of roller	1 nylon lateral roller diameter: 1.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By shifting conveyor belt
Product weight	0.1 lb(US)

Environment

ambient air temperature for operation	-20...185 °F
ambient air temperature for storage	-20...185 °F
environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will not be Compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.