





# 3.S.0

High precision tweezers - SS - tips: straight, very sharp, fine, superior finish. OAL: 120mm



4 3/4" 120 mm  
Very sharp, fine

## Documents

Body material TDS

## Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	High precision tweezers

<b>Kit</b>	no
<b>Tip style</b>	3
<b>Tip type characteristic</b>	fine, very sharp
<b>Bent / angled / curved tip (y/n)</b>	no
<b>Reverse action</b>	no
<b>Handle serration(y/n)</b>	no
<b>Tip serration (y/n)</b>	no
<b>Locking system</b>	no
<b>ESD safe</b>	no
<b>Body material</b>	S
<b>Product OAL (mm - in)</b>	120.00 - 4.724
<b>Product width (mm - in)</b>	10.00 - 0.394
<b>Product height (mm - in)</b>	11.00 - 0.433
<b>Tip thickness A (mm - in)</b>	0.10 - 0.004
<b>Tip width B (mm - in)</b>	0.15 - 0.006
<b>Tip opening gap (mm - in)</b>	8.00 - 0.315
<b>Net weight (g-lb)</b>	13 - 0.029
<b>RoHS compliant</b>	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com