



EXCELTA[®]
SINCE 1957

Product Specification Sheet

Excelta 9241E

Description: -★★★★★- Maximum Flush – Medium Round Head Cutter
Cutting Capacity: .005" - .040" (.13MM –1) Soft Copper Wire
Shape: Round Head
Cut Type: Maximum Flush
Material: Carbon Steel with Cushion ESD Safe grips (10¹⁰ ohms/sq)
Tip Size: .31" (7.75 mm)
Overall Length: 4.5" (112.5 mm)
Body Width: 0.42" (10.5 mm)
Body Height: 0.25" (6.88 mm)
Made in USA

The Lazer Line[®] medium oval head cutters are made of AISI 52100 carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the Lazerlok[™] joint surfaces to be perfect to allow for long life. The grips are soft cushioned foam and are ESD safe (10¹⁰ ohms/sq). The dual leaf springs provide smooth action.



EXCELTA[®]
SINCE 1957

T: 805-694-2169 | F: 805-686-9005