


XVS96BMBN

electronic alarm - 16 tones - 0..96 dB - NPN output - black - IP54



Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

Complementary

Colour	Black
Material	PC (polycarbonate) (terminal cover) PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene) (body)
Product weight	0.4 kg
Marking	CE
Overvoltage category	Class II conforming to EN/IEC 61140
Mounting support	96 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	250 mA at 12 V 292 mA at 12 V 292 mA at 24 V 354 mA at 24 V
Clamping connection capacity	<= 1 x 1.5 mm ²
Width	96 mm
Height	96 mm
Depth	58.1 mm

Environment

discrete output type	NPN
signalling type	16 tones alarm
standards	EN/IEC 60947-1 EN/IEC 60947-5-1
protective treatment	TC
ambient air temperature for storage	-35...70 °C
ambient air temperature for operation	-20...50 °C
IP degree of protection	IP54 (panel mounted) conforming to EN/IEC 60529
noise level	0...96 dB (continuous or intermittent tone) at 1 m

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1346 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Electronic Alarm

Dimensions

