



### Main

Range of product	Harmony XVB Universal
Product or component type	Complete beacon
Beacon or indicator bank unit type	Base unit with direct or tube fixing mode Illuminated unit
Signalling type	Steady
Mounting diameter	70 mm
Component name	XVBL
Material	Glass reinforced polyamide (base unit) Polycarbonate (illuminated unit)
Light source	Blue integral LED
Bulb type	Protected LED
[Us] rated supply voltage	230 V AC

### Complementary

Connections - terminals	Screw clamp terminals, connection capacity: <= 1 x 1.5 mm <sup>2</sup> with cable end
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 Un conforming to IEC 60947-5-1
Current consumption	< 17 mA AC
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
CAD overall width	70 mm
CAD overall height	139 mm
CAD overall depth	70 mm
Terminals description ISO n°1	(COM-1)PW (GND)GROUND
Product weight	0.27 kg

### Environment


pollution degree	2
product certifications	CCC CSA C22-2 No 14 GOST UL 508
standards	EN/IEC 60947-5-1
protective treatment	TC
ambient air temperature for storage	-40...70 °C
electrical shock protection class	Class I (on support tube) conforming to IEC 61140 Class II (on base unit) conforming to IEC 61140
IP degree of protection	IP65 (on fixing base XVBZ0.) conforming to IEC 60529 IP66 (on base unit) conforming to IEC 60529
NEMA degree of protection	NEMA 4X (indoor) conforming to UL 508

### Contractual warranty

Warranty period	18 months
-----------------	-----------

### Illuminated Beacon for BA 15d Bulb or LED

### Dimensions



## Illuminated Beacon

### Wiring Diagram

