



SAFETY DATA SHEET CARLUBE CHAINSAW OIL

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name CARLUBE CHAINSAW OIL

Product number XPM455, XPM011

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Chain oil.

1.3. Details of the supplier of the safety data sheet

Supplier TETROSYL LIMITED
Bury
Lancashire
England
BL9 7NY
0161 764 5981
0161 797 5899
info@tetrosyl.com

Manufacturer TETROSYL LIMITED
Bury
Lancashire
England
BL9 7NY
0161 764 5981
0161 797 5899
info@tetrosyl.com

1.4. Emergency telephone number

Emergency telephone +44 (0)161 764 5981

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Aquatic Chronic 3 - H412

Human health See Section 11 for additional information on health hazards.

2.2. Label elements

Hazard statements EUH208 Contains REACTION PRODUCTS OF BIS(4-METHYLPENTAN-2-YL)DITHIOPHOSPHORIC ACID WITH PHOSPHORUS OXIDE, PROPYLENE OXIDE AND AMINES, C12-14 ALKYL (BRANCHED). May produce an allergic reaction.
H412 Harmful to aquatic life with long lasting effects.

CARLUBE CHAINSAW OIL

Precautionary statements

P101 If medical advice is needed, have product container or label at hand.
 P102 Keep out of reach of children.
 P273 Avoid release to the environment.
 P501 Dispose of contents/ container in accordance with national regulations.

2.3. Other hazards

Not applicable.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

REACTION PRODUCTS OF BIS(4-METHYLPENTAN-2-YL)DITHIOPHOSPHORIC ACID WITH PHOSPHORUS OXIDE, PROPYLENE OXIDE AND AMINES, C12-14 ALKYL (BRANCHED)		0.1-<0.3%
CAS number: —	EC number: 931-384-6	REACH registration number: 01-2119493620-38-0000
Classification Acute Tox. 4 - H302 Eye Dam. 1 - H318 Skin Sens. 1 - H317 Aquatic Chronic 2 - H411		
OLEYLAMINE		0.1-<0.3%
CAS number: 112-90-3	EC number: 204-015-5	
M factor (Acute) = 10	M factor (Chronic) = 10	
Classification Acute Tox. 4 - H302 Skin Corr. 1B - H314 Eye Dam. 1 - H318 STOT SE 3 - H335 STOT RE 2 - H373 Asp. Tox. 1 - H304 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410		

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Remove affected person from source of contamination. Get medical attention if any discomfort continues.
Inhalation	Get medical attention if any discomfort continues.
Ingestion	Consult a physician for specific advice.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Do not rub eye.

CARLUBE CHAINSAW OIL

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure. Effects may be delayed. Keep affected person under observation.
Inhalation	May cause an asthma-like shortness of breath. Vapours may cause headache, fatigue, dizziness and nausea.
Ingestion	May cause discomfort if swallowed. May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.
Skin contact	Prolonged or repeated contact with skin may cause irritation, redness and dermatitis. Allergic rash.
Eye contact	May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations. If in doubt, get medical attention promptly.
-----------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards	Fire creates: Carbon monoxide (CO). Carbon dioxide (CO ₂). No unusual fire or explosion hazards noted.
Hazardous combustion products	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours. Oxides of carbon.

5.3. Advice for firefighters

Protective actions during firefighting	No specific firefighting precautions known.
Special protective equipment for firefighters	Leave danger zone immediately.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	For personal protection, see Section 8. In case of spills, beware of slippery floors and surfaces.
-----------------------------	--

6.2. Environmental precautions

Environmental precautions	Collect and dispose of spillage as indicated in Section 13.
----------------------------------	---

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	For waste disposal, see Section 13. Wear protective clothing as described in Section 8 of this safety data sheet. Provide adequate ventilation. Contain spillage with sand, earth or other suitable non-combustible material. Avoid the spillage or runoff entering drains, sewers or watercourses. Absorb spillage with non-combustible, absorbent material.
--------------------------------	---

6.4. Reference to other sections

Reference to other sections	Wear protective clothing as described in Section 8 of this safety data sheet. Collect and dispose of spillage as indicated in Section 13.
------------------------------------	---

CARLUBE CHAINSAW OIL

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions

Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Do not eat, drink or smoke when using the product. Avoid the formation of mists. Provide adequate ventilation. Avoid contact with skin and eyes. Always remove oil with soap and water or skin cleaning agent, never use organic solvents. Do not use oil-contaminated clothing or shoes, and do not put rags moistened with oil into pockets.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions

Keep containers upright. Store in tightly-closed, original container.

7.3. Specific end use(s)

Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

No exposure limits known for ingredient(s).

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Avoid inhalation of vapours. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. It is recommended that gloves are made of the following material: Nitrile rubber. It should be noted that liquid may penetrate the gloves. Frequent changes are recommended.

Other skin and body protection

Wear suitable protective clothing as protection against splashing or contamination.

Hygiene measures

Use engineering controls to reduce air contamination to permissible exposure level.

Respiratory protection

No specific recommendations.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Viscous liquid.

Colour

Brown.

Odour

Characteristic.

Odour threshold

Not determined.

pH

Not determined.

CARLUBE CHAINSAW OIL

Melting point	Not determined.
Initial boiling point and range	>250°C @ 1.013 hPa
Flash point	205°C
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	0.893g/cm ³ @ 20°C
Solubility(ies)	Insoluble in water.
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	200-240 mm ² /s @ 40°C
Oxidising properties	Not determined.

9.2. Other information

Other information	None.
--------------------------	-------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
-------------------	---

10.2. Chemical stability

Stability	No particular stability concerns.
------------------	-----------------------------------

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not applicable.
---	-----------------

10.4. Conditions to avoid

Conditions to avoid	Avoid heat, flames and other sources of ignition.
----------------------------	---

10.5. Incompatible materials

Materials to avoid	Strong oxidising agents.
---------------------------	--------------------------

10.6. Hazardous decomposition products

Hazardous decomposition products	Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.
---	--

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects	No information available.
------------------------------	---------------------------

Inhalation	No specific health hazards known.
-------------------	-----------------------------------

CARLUBE CHAINSAW OIL

Ingestion	May cause discomfort if swallowed.
Skin contact	Prolonged and frequent contact may cause redness and irritation. May cause an allergic skin reaction.
Eye contact	May cause temporary eye irritation.
Acute and chronic health hazards	Because of the product's quantity and composition, the health hazard is regarded as low.

SECTION 12: Ecological information

Ecotoxicity	Toxic to aquatic life with long lasting effects.
--------------------	--

12.1. Toxicity

Acute aquatic toxicity

Acute toxicity - fish	Not determined.
------------------------------	-----------------

Acute toxicity - aquatic invertebrates	Not determined.
---	-----------------

Acute toxicity - aquatic plants	Not determined.
--	-----------------

12.2. Persistence and degradability

Persistence and degradability	No data available.
--------------------------------------	--------------------

12.3. Bioaccumulative potential

Bioaccumulative potential	No data available on bioaccumulation.
----------------------------------	---------------------------------------

Partition coefficient	Not determined.
------------------------------	-----------------

12.4. Mobility in soil

Mobility	The product is insoluble in water.
-----------------	------------------------------------

Adsorption/desorption coefficient	Not available.
--	----------------

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment	This substance is not classified as PBT or vPvB according to current EU criteria.
---	---

12.6. Other adverse effects

Other adverse effects	Not available.
------------------------------	----------------

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	When handling waste, the safety precautions applying to handling of the product should be considered.
Disposal methods	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Absorb in vermiculite, dry sand or earth and place into containers. Dispose of waste via a licensed waste disposal contractor.

SECTION 14: Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).
----------------	--

14.1. UN number

CARLUBE CHAINSAW OIL

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations	The Control of Substances Hazardous to Health Regulations 2002 (SI 2002 No. 2677) (as amended).
EU legislation	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments	NOTE: Lines within the margin indicate significant changes from the previous revision.
Issued by	Health & Safety Department
Revision date	15/01/2019
Revision	11
Supersedes date	01/04/2016
SDS status	Approved.

CARLUBE CHAINSAW OIL

Hazard statements in full

H302 Harmful if swallowed.
H304 May be fatal if swallowed and enters airways.
H314 Causes severe skin burns and eye damage.
H317 May cause an allergic skin reaction.
H318 Causes serious eye damage.
H335 May cause respiratory irritation.
H373 May cause damage to organs through prolonged or repeated exposure.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
H411 Toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.
EUH208 Contains REACTION PRODUCTS OF BIS(4-METHYLPENTAN-2-YL)DITHIOPHOSPHORIC ACID WITH PHOSPHORUS OXIDE, PROPYLENE OXIDE AND AMINES, C12-14 ALKYL (BRANCHED). May produce an allergic reaction.

The information provided in this document has been compiled on the basis of our current knowledge and is believed to be in accordance with the requirements of the Dangerous Substances Directive, Dangerous Preparations Directive and Safety Data Sheets Directive. The information relates to the specific material designated and may not be valid for such material used in combination with any other materials or in any particular conditions or process. The conditions and extent of storage and use of material are outside of our control and within the control of the possessor or user. Consequently it is the responsibility of the possessor or user to satisfy themselves as to the completeness of such information and the suitability of the material for their own particular circumstances, conditions or use.