

**THM  
THM GEW 17/9 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

**General ordering data**

Type	THM GEW 17/9 GE
Order No.	<a href="#">1059810000</a>
Version	THM, Device markers, 9 x 17 mm, yellow
GTIN (EAN)	4032248808229
Qty.	1 pc(s).
compatible printer	<a href="#">2430920000</a> <a href="#">2448870000</a>

## THM THM GEW 17/9 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	17 mm	Width (inches)	0.669 inch
Height	9 mm	Height (inches)	0.354 inch
Depth	0.3 mm	Depth (inches)	0.012 inch
Net weight	595 g		

### General data

Adhesive	Natural rubber adhesive	Approval acc. to UL 969	No
Colour	yellow	Halogen	No
Material	Cotton fabric	Material colour according to resistance code	4
Number per roll	10,000	Number per sheet	10,000
Operating temperature range	-29...80 °C	Printing method	Thermotransfer
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	17 mm		

### Classifications

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	55-12-16-00	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>
Software	<a href="#">M-Print PRO configuration file</a>

**Data sheet**

**THM  
THM GEW 17/9 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**Data sheet**

**THM  
THM GEW 17/9 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**Ink ribbons**



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM 110/360 SW	<a href="#">2005070000</a>	Ink ribbon	4050118390049	1 pc(s).

**Data sheet**

**THM  
THM GEW 17/9 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

