

HS 2.1-6.4/25 MM W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



MultiMark

With MultiMark you have a fast and reliable marking system at your disposal to enable virtually any kind of marking. Connectors, conductors, cables or devices – the MultiMark product family offers a well-structured, practical range of markers which can be used in combination with our advanced M-Print® PRO configuration software for all areas of use.

Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

General ordering data

Type	HS 2.1-6.4/25 MM W
Order No.	2437630000
Version	Conductor and cable markers, 2.1 - 6.4 mm, 25.4 x 10.7 mm, white
GTIN (EAN)	4050118461381
Qty.	2,000 pc(s).
compatible printer	2430920000 2448870000 1140490000

HS 2.1-6.4/25 MM W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	10.7 mm	Width (inches)	0.421 inch
Height	25.4 mm	Height (inches)	1 inch
Depth	0.77 mm	Depth (inches)	0.03 inch
Net weight	0.3 g		

General data

Colour	white	Halogen	Yes
Material	Polyolefine	Number per roll	2,000
Operating temperature range	-55...135 °C	Recommended industries	Plant manufacture, Energy, Device manufacturer, Machinery
Width	10.7 mm		

Conductor and cable markers

Conductor O.D.	2.1 - 6.4 mm	Conductor O.D., max.	6.4 mm
Conductor O.D., min.	2.1 mm	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	1.5 mm ²	Halogen	Yes
Rate of shrinkage	3:1	Recommended shrinking temperature	90 °C

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	EPLAN
------------------	-----------------------

Data sheet

HS 2.1-6.4/25 MM W

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



HS 2.1-6.4/25 MM W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories

Ink ribbons



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM- HS 60/300 SW	2448880000	Ink ribbon	4050118462944	1 pc(s).

Accessories / replacement parts



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
THM MMP ROLLER 115	1357420000		4050118160314	1 pc(s).