

**THM**  
**THM WO 33.5/93.1 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

#### General ordering data

Type	THM WO 33.5/93.1 WS
Order No.	<a href="#">1774400000</a>
Version	THM, Conductor and cable markers, 8 - 21.7 mm, 33.5 x 93.1 mm, white
GTIN (EAN)	4032248148585
Qty.	1 pc(s).
compatible printer	<a href="#">2430920000</a> <a href="#">2448870000</a>

**THM**  
**THM WO 33.5/93.1 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	93.1 mm	Width (inches)	3.665 inch
Height	33.5 mm	Height (inches)	1.319 inch
Depth	0.025 mm	Depth (inches)	0.001 inch
Net weight	286 g		

**General data**

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester film	Material colour according to resistance code	9
Number per roll	500	Operating temperature range	-40... 150 °C
Size of labelling field	25 x 33.5 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	93.1 mm		

**Conductor and cable markers**

Conductor O.D.	8 - 21.7 mm	Conductor O.D., max.	21.7 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	400 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Halogen	No

**Classifications**

ETIM 3.0	EC001530	ETIM 4.0	EC001288
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

**Approvals**

ROHS	Conform
------	---------

**Downloads**


Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
Software	<a href="#">M-Print PRO configuration file</a>

**Data sheet**

**THM**  
**THM WO 33.5/93.1 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**Data sheet**

**THM  
THM WO 33.5/93.1 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Accessories**

**Ink ribbons**



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM 110/360 SW	<a href="#">2005070000</a>	Ink ribbon	4050118390049	1 pc(s).