M12 EMI/RFI Shielded Rear Panel Mount Connectors, A-Coded, MPM12-SS Series







Plug

Receptacle

Electrical Values

Rated Voltage : 250V (3 - 4 contacts) IEC 61076-2-101 : 60V (5 contacts) 30V (8 contacts)

Rated Current : 4A (3 - 4 contacts) IEC 61076-2-101 : 4A (5 contacts) 2A (5 - 8 contacts)

Volume Resistance

Mating Cycles :>100 IEC 60512-9A Pollution Degree : 3 IEC 60664-1

Specifications

General Values

Connector : M12 Plug and Receptacle

Termination : Solder : ≤ 4mm Panel Thickness

Temp. Range : -25°C to +85°C IEC 60664-1

: IP67 IEC 60529 IP Rating


Mounting Torque : 60 Ncm


Material

Contact Material : CuZn, Brass alloy Contact Plating : Au-plated, Au over Ni Contact Body Material : PA, Polyamide Housing Material : CuZn, Brass alloy : Ni-plated, Ni over Cu Plating Housing

: FKM O-ring

Diagram















Dimensions: Millimetres

Female Part Number Table

Description	Part Number
M12 Connector, Plug, A-Code, 3 Pins	MPM12-SSP-3ARP
M12 Connector, Plug, A-Code, 4 Pins	MPM12-SSP-4ARP
M12 Connector, Plug, A-Code, 5 Pins	MPM12-SSP-5ARP
M12 Connector, Plug, A-Code, 8 Pins	MPM12-SSP-8ARP
M12 Connector, Receptacle, A-Code, 3 Sockets	MPM12-SSS-3ARP
M12 Connector, Receptacle, A-Code, 4 Sockets	MPM12-SSS-4ARP
M12 Connector, Receptacle, A-Code, 5 Sockets	MPM12-SSS-5ARP
M12 Connector, Receptacle, A-Code, 8 Sockets	MPM12-SSS-8ARP

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness. any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

