



Main

Range of product	OsiSense XC
Series name	Standard format
Device short name	XCKM
Material	Metal
Body material	Zamak
Fixing mode	By the body
Movement of operating head	Linear

Complementary

Number of steps	1
Minimum force for tripping	12 N
Maximum actuation speed	0.5 m/s
Width	64 mm
Height	64 mm
Depth	30 mm

Environment

Ambient air temperature for operation	-25...70 °C
Standards	-

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile