



Main

Range of product	OsiSense XU
Series name	Application assembly
Specific application of photoelectric detector	Detection of items exiting an oven (high temperature fibers) Detection in aggressive environments Monitoring position or presence of parts on an assembly or packing machine Detection of presence of parts in a plastic mould
Sensor name	XUY
Sensor design	Fiber design
Emission	Red LED

Complementary

Electronic sensor type	Photo-electric sensor
Material	Plastic
Enclosure material	Polycarbonate
Pulse frequency	8 kHz
Type of output signal	Discrete
Output type	Solid state
Discrete output function	1 NO or 1 NC programmable
Discrete output type	PNP and NPN
Electrical connection	1 male connector M8, 4 pins
Supply circuit type	DC
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Supply voltage limits	10...30 V DC
Voltage state 0 guaranteed	< 1.4 V
Voltage state 1 guaranteed	> 3 V
Switching capacity in mA	100 mA (overload and short-circuit protection)
Switching frequency	< 1 kHz
Maximum voltage drop	<2 V (closed state)
Current consumption	<= 40 mA no-load
Maximum delay response	5 ms for glass fibre optics 3 mm
Maximum delay recovery	5 ms glass fibre optics 3 mm
Setting-up	Sensitivity adjustment using +/- teach mode

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Display type	Bar graph
Net weight	0.047 kg

Environment

Product certifications	CE CULus
Ambient air temperature for operation	0...60 °C
Ambient air temperature for storage	-20...80 °C
Immunity to ambient light	10000 lux natural light 20000 lux incandescent bulb
IP degree of protection	IP65 conforming to IEC 60529

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

Contractual warranty

Warranty	18 months
----------	-----------