

8 Pin In-Line DIN Plug


**RoHS
Compliant**



Specifications

Rating	: 100V AC 1A Max.
Contact Resistance	: Pin 30mΩ Max., shell 50mΩ Max.
Insulation Resistance	: Min. 100MΩ @ 500V DC
Voltage Withstand	: 250V AC RMS for 1 minute

Diagram



Dimensions : Millimetres

No.	Description	Material	Treat	Qty.
1	YE-115X Shell Cover 6.0	EVA+LLDPE	-	1
2	Shield Cover A	Steel	Nickel Plated	
3	Shield Cover B	Steel	Nickel Plated	
4	8P270 Housing	ABS	-	
5	Contact Terminals	Brass	Nickel Plated	8

Part Number Table

Description	Part Number
8 Pin In-Line DIN Plug	27-675

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MCM is the registered trademark of Premier Farnell Limited 2019.