

## R18PDBL-0 | 18V Cordless Brushless Percussion Drill



- Brushless percussion drill ideal for drilling in wood or metal, driving screws or even drilling in masonry thanks to the hammer function.
- Ryobi's Brushless technology uses patented electronics to deliver more runtime and power.
- All metal 13mm ratcheting chuck for improved bit gripping strength and durability.
- 2 gears to control the max speed to match different materials and applications.
- e-Torque control settings make it easy to drive screws flush everytime.
- LED lights up your work area for better visibility.

	R18PDBL-0
Battery pack capacity (Ah)	-
Battery type	Li-ion
Charger included?	No
Chuck capacity (mm)	13
Max drilling steel (mm)	13
Max. drilling masonry (mm)	13
Max. drilling wood (mm)	50
Max. percussion rate (bpm)	7040 / 27200
Max. torque (Nm)	60
No load speed (rpm)	0-440 / 0-1700
No. of batteries supplied	0
Power	18V
Sound power level [dB(A)]	92.5
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	81.5
Sound pressure level uncertainty [dB(A)]	3.0
Supplied in	Recyclable Carton
Torque settings	10
Vibration drilling into concrete [m/s <sup>2</sup> ]	9.0
Vibration drilling into concrete uncertainty [m/s <sup>2</sup> ]	1.5
Vibration drilling into Metal [m/s <sup>2</sup> ]	1.9
Vibration drilling into metal uncertainty [m/s <sup>2</sup> ]	1.5
Vibration screw driving [m/s <sup>2</sup> ]	1.8
Vibration screw driving uncertainty [m/s <sup>2</sup> ]	1.5