



### Main

Range of product	Preventa Safety detection
Product or component type	Guard switch
Component name	XCSPR
Material	Plastic
Head type	Turret head rotary axis
Insulation	Double insulated
Type of operator	Spindle 30 mm
Electrical connection	Terminal
Contacts type and composition	1 NC + 1 NC + 1 NO
Contact operation	Slow-break, break before make
Clamping connection capacity	1 x 0.34...2 x 0.75 mm <sup>2</sup> with or without cable end
Cable entry	1 entry tapped Pg 11
Number of poles	3

### Complementary

Cable outer diameter	7...10 mm
Positive opening	With NC contact
Tripping angle	5 °
Mechanical durability	1000000 cycles
Minimum torque for tripping	0.1 N.m
Positive opening minimum torque	0.25 N.m
Minimum actuation speed	0.1 m/s
Contact code designation	B300, AC-15 (U <sub>e</sub> = 120 V, I <sub>e</sub> = 6 A) conforming to EN/IEC 60947-5-1 B300, AC-15 (U <sub>e</sub> = 240 V, I <sub>e</sub> = 3 A) conforming to EN/IEC 60947-5-1 Q300, DC-13 (U <sub>e</sub> = 125 V, I <sub>e</sub> = 0.2 A) conforming to EN/IEC 60947-5-1 R300, DC-13 (U <sub>e</sub> = 250 V, I <sub>e</sub> = 0.1 A) conforming to EN/IEC 60947-5-1
[I <sub>th</sub> ] conventional enclosed thermal current	6 A
[U <sub>i</sub> ] rated insulation voltage	300 V conforming to CSA C22.2 No 14

400 V (degree of pollution: 3) conforming to EN/IEC 60947-1  
300 V conforming to UL 508

[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60947-5-1
Resistance across terminals	<= 30 mOhm conforming to EN/IEC 60947-5-4
Short-circuit protection	6 A cartridge fuse type gG (gl)
Safety level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety reliability data	B10d = 5000000 (value given for a life time of 20 years limited by mechanical or contact wear)
Enclosure material	Polyamide PA66 fibre glass impregnated
Lever material	Stainless steel
Product weight	0.105 kg

## Environment

Standards	EN 1088/ISO 14119 EN/IEC 60204-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/ISO 12100 UL 508 CSA C22.2 No 14
Product certifications	BG CSA UL
Protective treatment	TC TH
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	50 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to EN/IEC 61140
IP degree of protection	IP67 conforming to IEC 60529

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1136 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------