



Main

Product or component type	Dv/dt filter
Range compatibility	Altivar Easy 610 Altivar Process ATV600 Altivar Process ATV900 Altivar Machine ATV340
Product specific application	Output filter
[In] rated current	6 A
Product compatibility	Variable speed drive ATV630 wall mount, motor: 0.75 kW 380...480 V Variable speed drive ATV630 wall mount, motor: 1.5 kW 380...480 V Variable speed drive ATV630 wall mount, motor: 2.2 kW 380...480 V Variable speed drive ATV630 wall mount, motor: 0.75 kW 200...240 V Variable speed drive ATV650 wall mount, motor: 0.75 kW 380...480 V Variable speed drive ATV650 wall mount, motor: 1.5 kW 380...480 V Variable speed drive ATV650 wall mount, motor: 2.2 kW 380...480 V Variable speed drive ATV610 motor: 0.75 kW 380...415 V Variable speed drive ATV610 motor: 1.5 kW 380...415 V Variable speed drive ATV610 motor: 2.2 kW 380...415 V Variable speed drive ATV930 wall mount, motor: 0.75 kW 380...480 V Variable speed drive ATV930 wall mount, motor: 1.5 kW 380...480 V Variable speed drive ATV930 wall mount, motor: 2.2 kW 380...480 V Variable speed drive ATV930 wall mount, motor: 0.75 kW 200...240 V Variable speed drive ATV950 wall mount, motor: 0.75 kW 380...480 V Variable speed drive ATV950 wall mount, motor: 1.5 kW 380...480 V Variable speed drive ATV950 wall mount, motor: 2.2 kW 380...480 V
Nedded quantity	1
Electrical connection	Terminal block, connection capacity: 4 mm ² / AWG 12

Complementary

Motor cable length	<= 300 m shielded cable at 4 kHz <= 300 m unshielded cable at 4 kHz
DV/Dt	3000 V/μs max at 200...240 V 3000 V/μs max at 380...480 V
Thermal losses	16 W 4 kHz
Maximum drive output frequency	<= 100 Hz
Ambient air temperature for operation	50...60 °C with current derating 1.5 % per °C -10...50 °C without current derating
Operating altitude	0...1000 m without current derating 1000...4000 m with current derating 1 % per 100 m

Width	285 mm
Height	530 mm
Depth	215 mm
Product weight	11 kg

Environment

IP degree of protection	IP21 (with kit VW3A53902) IP20
Ambient air temperature for storage	-40...70 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1451 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---