

### Main

Product or component type	Sinus filter
Range compatibility	Altivar Process ATV600 Altivar Process ATV900
Product specific application	Output filter

### Complementary


Motor cable length	<= 1000 m unshielded cable <= 500 m shielded cable
[In] rated current	305 A
Thermal losses	676 W at 4 kHz
Product compatibility	Variable speed drive ATV630 wall mount, motor: 110 kW, 380...480 V Variable speed drive ATV630 wall mount, motor: 132 kW, 380...480 V Variable speed drive ATV630 wall mount, motor: 55 kW, 200...240 V Variable speed drive ATV930 wall mount, motor: 110 kW, 380...480 V Variable speed drive ATV930 wall mount, motor: 132 kW, 380...480 V Variable speed drive ATV930 wall mount, motor: 55 kW, 200...240 V
Electrical connection	Copper bar M10
Operating altitude	1000...4000 m with current derating 1 % per 100 m <= 1000 m without current derating
Switching frequency	2...6 kHz
Output frequency	<= 100 Hz
Voltage drop at rated load	< 8 %
Permissible voltage	<= 480 V AC
Max current	1.20 x nominal current for 60 s
Width	460 mm
Height	370 mm
Depth	565 mm
Product weight	131 kg

### Environment

IP degree of protection	IP00
Environmental characteristic	Biological pollution resistance class 3B1 conforming to IEC 60721-3-3 Chemical pollution resistance class 3C3 conforming to IEC 60721-3-3 Dust pollution resistance class 3S3 conforming to IEC 60721-3-3

Pollution degree	3 conforming to IEC 61800-5-1
Relative humidity	5...95 % without condensation
Ambient air temperature for operation	50...60 °C with current derating 1.5 % per °C -15...50 °C without current derating
Ambient air temperature for storage	-40...70 °C
Mechanical robustness	Shocks conforming to IEC 60721-3-3 class 3M4 Vibrations conforming to IEC 60721-3-3 class 3M4

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1451 - Schneider Electric declaration of conformity  <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---