



### Main

Range of product	Harmony XVS
Product or component type	Multisound siren
Device short name	XVS

### Complementary

Colour	White
Material	PC (polycarbonate) (back cover) PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene) (front) PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene) (back)
Product weight	1.2 kg
Marking	CE
Mounting support	Bracket
Fixing mode	3 holes Ø 9 mm
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	100 mA at 120 V
Electrical connection	Cable : 6.5...8.5 mm, 0.33 mm <sup>2</sup> / AWG 22 (signalling circuit) Cable : 6.5...8.5 mm, 0.52 mm <sup>2</sup> / AWG 20 (power circuit)
Width	140 mm
Height	114 mm
Depth	223 mm

### Environment

Signalling type	43 tones siren
Standards	EN 60947 EN 60947-5 EN 61000-6-2 EN 61000-6-3
Product certifications	UL
Protective treatment	TC

Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Overvoltage category	Class II conforming to EN/IEC 61140
IP degree of protection	IP53 conforming to EN/IEC 60529
[Us] rated supply voltage	120 V AC
Noise level	0...105 dB (continuous or intermittent tone) at 1 m

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1611 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Siren

Dimensions

mm  
in.

