Product data sheet Characteristics

ABL8TEQ24300

rectified and filtered power supply - 3-phase - 400 V AC - 24 V - 30 A



Wichin		
Range of product	Phaseo Rectified	- -
Product or component type	Power supply	
Power supply type	Rectified and filtered	
Rated power in W	720 W	
Input voltage	400 V AC three phase, terminal(s): L1, L2, L3	
Output voltage	24 V DC	-
Power supply output current	30 A	
Operating position	Horizontal at 40 °C Vertical at 55 °C	

Complementary

Main			
Range of product	Phaseo Rectified		
Product or component type	Power supply		
Power supply type	Rectified and filtered		
Rated power in W	720 W		
Input voltage	400 V AC three phase, terminal(s): L1, L2, L3		
Output voltage	24 V DC		
Power supply output current	30 A		
Operating position	Horizontal at 40 °C Vertical at 55 °C		
Complementary			
Input voltage limits	360440 V		
Network frequency limits	4763 Hz		
Input voltage tolerance	+/- 20 V		
Inrush current	20 A at 400 V		
Cos phi	0.835 at 400 V		
Efficiency	77 %		
Power dissipation in W	165 W		
Holding time	7 ms		
Output protection type	Against overload and short-circuits, protection technology: external fuse, 40 A Against overvoltage, protection technology: 2 J peak limiter		
Connections - terminals	Screw type terminals for input ground connection, connection capacity: 1 x 2.51 x 4 mm² AWG 14AWG 11 Screw type terminals for input connection, connection capacity: 9 x 2.59 x 4 mm² AWG 14AWG 11 Screw type terminals for output connection, connection capacity: 4 x 104 x 16 mm² AWG 8AWG 6		
Marking	CE		
Fixing mode	By 4 screws		
Output coupling	Parallel Series		
Operating altitude	3000 m		
Name of test	Conducted/radiated emissions conforming to EN 55011 class B Electrostatic discharges conforming to EN/IEC 61000-4-2		
Jul 1 2019			

Emission conforming to EN 50081-1
Emission conforming to EN 61000-6-3
Rapid transient conforming to IEC 61000-4-4
Surge conforming to EN/IEC 61000-4-5

Status LED	1 LED green for output voltage		
Depth	108 mm		
Height	252 mm		
Width	240 mm		
Product weight	13 kg		

Environment

Product certifications	KC UL 508 EAC
	cULus
Environmental characteristic	EMC conforming to EN/IEC 61000-3-2 EMC conforming to IEC 62041 Safety conforming to EN/IEC 61558-2-6 Safety conforming to UL 508 Safety conforming to UL 60950-1
IP degree of protection	IP20 conforming to EN/IEC 60529
Ambient air temperature for operation	-2055 °C
Ambient air temperature for storage	-4080 °C
Relative humidity	095 % without condensation or dripping water
Electrical shock protection class	Class I conforming to VDE 0106-1
Dielectric strength	2000 V between input and ground 4600 V between input and output 500 V between output and ground


Contractual warranty

Warranty period	18 months		

Product data sheet Dimensions Drawings

ABL8TEQ24300

Dimensions



Dimensions in mm

а	b	С	G	J	Ø
240	252	108	220	87	8


Dimensions in in.

а	b	С	G	J	Ø
9.45	9.92	4.25	8.66	3.42	0.31

Product data sheet Connections and Schema

ABL8TEQ24300


Internal Wiring Diagram



Product data sheet Performance Curves

ABL8TEQ24300

Load Limits Curve



- Nominal line supply + 10%
- (1) (2) (3) Nominal line supply
 Nominal line supply - 10%