

# SAFETY DATA SHEET

Alloy Sn63-Pb37 NC 254



## Section 1. Identification

**Product identifier** : Alloy Sn63-Pb37 NC 254  
**Other means of identification** : Not available.  
**Product type** : Solid: Paste

### Relevant identified uses of the substance or mixture and uses advised against

Not applicable.

**Supplier's details** : AIM  
9100 Henri Bourassa East  
Montreal, QC  
H1E 2S4  
(514) 494-2000  
  
In the United States:  
AIM  
25 Kenney Drive  
Cranston, RI 02920  
(800) CALL-AIM

**Emergency telephone number (with hours of operation)** : INFOTRAC  
North America: (800) 535-5053  
International: (352) 323-3500

## Section 2. Hazard(s) identification

**Classification of the substance or mixture** : SKIN SENSITIZATION - Category 1  
CARCINOGENICITY - Category 1B  
TOXIC TO REPRODUCTION (Fertility) - Category 1B  
TOXIC TO REPRODUCTION (Unborn child) - Category 1B  
SPECIFIC TARGET ORGAN TOXICITY (REPEATED EXPOSURE) - Category 2  
Percentage of the mixture consisting of ingredient(s) of unknown toxicity: 1.2%

### GHS label elements

**Hazard pictograms** :



**Signal word** : **DANGER**  
**Hazard statements** : **May cause an allergic skin reaction.**  
**May cause cancer.**  
**May damage fertility or the unborn child.**  
**May cause damage to organs through prolonged or repeated exposure.**

### Precautionary statements

**General** : Not applicable.  
**Prevention** : Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Use personal protective equipment as required. Wear protective gloves. Do not breathe dust. Contaminated work clothing should not be allowed out of the workplace.  
**Response** : Get medical attention if you feel unwell. IF exposed or concerned: Get medical attention. IF ON SKIN: Wash with plenty of soap and water. Wash contaminated clothing before reuse. If skin irritation or rash occurs: Get medical attention.

## Section 2. Hazard(s) identification

- Storage** : Store locked up.
- Disposal** : Dispose of contents and container in accordance with all local, regional, national and international regulations.
- Supplemental label elements** : Not applicable.
- Other hazards which do not result in classification** : None known.

## Section 3. Composition and ingredient information

- Substance/mixture** : Mixture
- Other means of identification** : Not available.

### CAS number/other identifiers

- CAS number** : Not applicable.
- EC number** : Mixture.
- Reference number** : GHS004

Ingredient name	% (w/w)	CAS number
tin	≥30 - ≤60	7440-31-5
lead powder	≥30 - ≤60	7439-92-1
Rosin, hydrogenated	≤5	65997-06-0

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

## Section 4. First aid measures

### Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Get medical attention.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Skin contact** : Wash with plenty of soap and water. Remove contaminated clothing and shoes. Wash contaminated clothing thoroughly with water before removing it, or wear gloves. Continue to rinse for at least 10 minutes. Get medical attention. In the event of any complaints or symptoms, avoid further exposure. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

### Most important symptoms/effects, acute and delayed

## Section 4. First aid measures

### Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : May cause an allergic skin reaction.
- Ingestion** : No known significant effects or critical hazards.

### Over-exposure signs/symptoms

- Eye contact** : No specific data.
- Inhalation** : Adverse symptoms may include the following:  
reduced fetal weight  
increase in fetal deaths  
skeletal malformations
- Skin contact** : Adverse symptoms may include the following:  
irritation  
redness  
reduced fetal weight  
increase in fetal deaths  
skeletal malformations
- Ingestion** : Adverse symptoms may include the following:  
reduced fetal weight  
increase in fetal deaths  
skeletal malformations

### Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.

See toxicological information (Section 11)

## Section 5. Fire-fighting measures

### Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

**Specific hazards arising from the chemical** : No specific fire or explosion hazard.

- Hazardous thermal decomposition products** : Decomposition products may include the following materials:  
carbon dioxide  
carbon monoxide  
metal oxide/oxides

**Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

**Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

## Section 6. Accidental release measures

### Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### Methods and materials for containment and cleaning up

- Small spill** : Move containers from spill area. Avoid dust generation. Do not dry sweep. Vacuum dust with equipment fitted with a HEPA filter and place in a closed, labeled waste container. Place spilled material in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Avoid dust generation. Do not dry sweep. Vacuum dust with equipment fitted with a HEPA filter and place in a closed, labeled waste container. Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

## Section 7. Handling and storage

### Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Persons with a history of skin sensitization problems should not be employed in any process in which this product is used. Avoid exposure - obtain special instructions before use. Avoid exposure during pregnancy. Do not handle until all safety precautions have been read and understood. Do not get in eyes or on skin or clothing. Do not ingest. If during normal use the material presents a respiratory hazard, use only with adequate ventilation or wear appropriate respirator. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

- Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Store locked up. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

## Section 8. Exposure controls and personal protection

### Control parameters

#### Occupational exposure limits

tin	<b>Safe Work Australia (Australia, 4/2018).</b> TWA: 2 mg/m <sup>3</sup> 8 hours.
lead powder	<b>Safe Work Australia (Australia, 4/2018).</b> TWA: 0.05 mg/m <sup>3</sup> , (as Pb) 8 hours. Form: Dust and fumes

**Appropriate engineering controls** : If user operations generate dust, fumes, gas, vapor or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits.

**Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

### Individual protection measures

**Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

**Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.

#### Skin protection

**Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.

**Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

## Section 9. Physical and chemical properties

### Appearance

<b>Physical state</b>	: Solid. [Solder Paste]
<b>Color</b>	: Not available.
<b>Odor</b>	: Not available.
<b>Odor threshold</b>	: Not available.
<b>pH</b>	: Not available.
<b>Melting point</b>	: Not available.

## Section 9. Physical and chemical properties

<b>Boiling point</b>	: Not available.
<b>Flash point</b>	: Not available.
<b>Evaporation rate</b>	: Not available.
<b>Flammability (solid, gas)</b>	: Not available.
<b>Lower and upper explosive (flammable) limits</b>	: Not available.
<b>Vapor pressure</b>	: Not available.
<b>Vapor density</b>	: Not available.
<b>Relative density</b>	: Not available.
<b>Solubility</b>	: Not available.
<b>Partition coefficient: n-octanol/water</b>	: Not available.
<b>Auto-ignition temperature</b>	: Not available.
<b>Decomposition temperature</b>	: Not available.
<b>Viscosity</b>	: Not available.
<b>Type of aerosol</b>	: Not applicable.
<b>Ignition distance</b>	: Not applicable.
<b>Enclosed space ignition - Time equivalent</b>	: Not applicable.
<b>Enclosed space ignition - Deflagration density</b>	: Not applicable.
<b>Flame height</b>	: Not applicable.
<b>Flame duration</b>	: Not applicable.

## Section 10. Stability and reactivity

<b>Reactivity</b>	: No specific test data related to reactivity available for this product or its ingredients.
<b>Chemical stability</b>	: The product is stable.
<b>Possibility of hazardous reactions</b>	: Under normal conditions of storage and use, hazardous reactions will not occur.
<b>Conditions to avoid</b>	: No specific data.
<b>Incompatible materials</b>	: No specific data.
<b>Hazardous decomposition products</b>	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## Section 11. Toxicological information

### Information on toxicological effects

#### Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Rosin, hydrogenated	LD50 Oral	Guinea pig	5000 mg/kg	-
	LD50 Oral	Rat	8400 mg/kg	-
Rosin, hydrogenated	LD50 Oral	Rat	>32000 mg/kg	-

#### Irritation/Corrosion

Not available.

#### Sensitization

## Section 11. Toxicological information

Not available.

### Mutagenicity

Not available.

### Carcinogenicity

Not available.

### Reproductive toxicity

Not available.

### Teratogenicity

Not available.

### Specific target organ toxicity (single exposure)

Not available.

### Specific target organ toxicity (repeated exposure)

Name	Category	Route of exposure	Target organs
lead powder	Category 2	Not determined	Not determined

### Aspiration hazard

Not available.

**Information on the likely routes of exposure** : Not available.

### Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : May cause an allergic skin reaction.
- Ingestion** : No known significant effects or critical hazards.

### Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : No specific data.
- Inhalation** : Adverse symptoms may include the following:  
reduced fetal weight  
increase in fetal deaths  
skeletal malformations
- Skin contact** : Adverse symptoms may include the following:  
irritation  
redness  
reduced fetal weight  
increase in fetal deaths  
skeletal malformations
- Ingestion** : Adverse symptoms may include the following:  
reduced fetal weight  
increase in fetal deaths  
skeletal malformations

### Delayed and immediate effects and also chronic effects from short and long term exposure

#### Short term exposure

- Potential immediate effects** : Not available.
- Potential delayed effects** : Not available.

#### Long term exposure



## Section 11. Toxicological information

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

### Potential chronic health effects

Not available.

**General** : May cause damage to organs through prolonged or repeated exposure. Once sensitized, a severe allergic reaction may occur when subsequently exposed to very low levels.

**Carcinogenicity** : May cause cancer. Risk of cancer depends on duration and level of exposure.

**Mutagenicity** : No known significant effects or critical hazards.

**Teratogenicity** : May damage the unborn child.

**Developmental effects** : No known significant effects or critical hazards.

**Fertility effects** : May damage fertility.

### Numerical measures of toxicity

#### Acute toxicity estimates

Not available.

## Section 12. Ecological information

### Toxicity

Product/ingredient name	Result	Species	Exposure
lead powder	Acute EC50 105 ppb Marine water	Algae - Chaetoceros sp. - Exponential growth phase	72 hours
	Acute EC50 0.489 mg/l Marine water	Algae - Ulva pertusa	96 hours
	Acute EC50 8000 µg/l Fresh water	Aquatic plants - Lemna minor	4 days
	Acute LC50 530 µg/l Fresh water	Crustaceans - Ceriodaphnia reticulata	48 hours
	Acute LC50 0.594 mg/l Fresh water	Daphnia - Daphnia magna	48 hours
	Acute LC50 0.44 ppm Fresh water	Fish - Cyprinus carpio - Juvenile (Fledgling, Hatchling, Weanling)	96 hours
	Chronic NOEC 0.25 mg/l Marine water	Algae - Ulva pertusa	96 hours
	Chronic NOEC 0.03 µg/l Fresh water	Fish - Cyprinus carpio	4 weeks

### Persistence and degradability

Not available.

### Bioaccumulative potential

Product/ingredient name	LogP <sub>ow</sub>	BCF	Potential
Rosin, hydrogenated	3.42	-	low
Rosin, hydrogenated	3.42	-	low

### Mobility in soil

**Soil/water partition coefficient (K<sub>oc</sub>)** : Not available.

**Other adverse effects** : No known significant effects or critical hazards.



## Section 13. Disposal considerations

**Disposal methods** : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

## Section 14. Transport information

	ADG	ADR/RID	IMDG	IATA
UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
UN proper shipping name	-	-	-	-
Transport hazard class(es)	-	-	-	-
Packing group	-	-	-	-
Environmental hazards	No.	No.	No.	No.
Additional information	-	-	-	-

**Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

**Transport in bulk according to Annex II of MARPOL and the IBC Code** : Not available.

## Section 15. Regulatory information

### Standard Uniform Schedule of Medicine and Poisons

Not regulated.

### Model Work Health and Safety Regulations - Scheduled Substances

<u>Ingredient name</u>	<u>Schedule</u>
tin	Restricted hazardous chemical [For abrasive blasting at a concentration of greater than 0.1% as tin]
lead powder	Restricted hazardous chemical [For abrasive blasting at a concentration of greater than 0.1% as lead or which would expose the operator to levels in excess of those set in the regulations covering lead]

**Australia inventory (AICS)** : Not determined.

### International regulations

## Section 15. Regulatory information

### [Chemical Weapon Convention List Schedules I, II & III Chemicals](#)

Not listed.

### [Montreal Protocol \(Annexes A, B, C, E\)](#)

Not listed.

### [Stockholm Convention on Persistent Organic Pollutants](#)

Not listed.

### [Rotterdam Convention on Prior Informed Consent \(PIC\)](#)

Not listed.

### [UNECE Aarhus Protocol on POPs and Heavy Metals](#)

Ingredient name	List name	Status
lead powder	Heavy metals - Annex 1	Listed

### [International lists](#)

#### [National inventory](#)

<b>Canada</b>	: Not determined.
<b>China</b>	: Not determined.
<b>Europe</b>	: Not determined.
<b>Japan</b>	: <b>Japan inventory (ENCS)</b> : Not determined. <b>Japan inventory (ISHL)</b> : Not determined.
<b>Malaysia</b>	: Not determined.
<b>New Zealand</b>	: Not determined.
<b>Philippines</b>	: Not determined.
<b>Republic of Korea</b>	: Not determined.
<b>Taiwan</b>	: Not determined.
<b>United States</b>	: All components are listed or exempted.

## Section 16. Any other relevant information

### [History](#)

**Date of printing** : 7/9/2019

**Date of issue/Date of revision** : 7/9/2019

**Date of previous issue** : 7/9/2019

**Version** : 0.02

**Key to abbreviations** : ADG = Australian Dangerous Goods  
ATE = Acute Toxicity Estimate  
BCF = Bioconcentration Factor  
GHS = Globally Harmonized System of Classification and Labelling of Chemicals  
IATA = International Air Transport Association  
IBC = Intermediate Bulk Container  
IMDG = International Maritime Dangerous Goods  
LogPow = logarithm of the octanol/water partition coefficient  
MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)  
NOHSC = National Occupational Health and Safety Commission  
SUSMP = Standard Uniform Schedule of Medicine and Poisons  
UN = United Nations

### [Procedure used to derive the classification](#)

**Section 16. Any other relevant information**

Classification	Justification
Skin Sens. 1, H317 Carc. 1B, H350 Repr. 1B, H360 (Fertility) Repr. 1B, H360 (Unborn child) STOT RE 2, H373	Calculation method Calculation method Calculation method Calculation method Calculation method

**References** : Not available.

✔ Indicates information that has changed from previously issued version.

**Notice to reader**

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.