


AC/DC Medical Power Supply

TPP 65A Series, 65 Watt

- Open frame power supply with pin connection
- Certification according to IEC/EN/ES 60601-1 3rd edition for 2 x MOPP
- Low leakage current <75 μA rated for BF applications
- Risk management process according to ISO 14971 incl. risk management file
- Acceptance criteria for electronic assemblies acc. to IPC-A-610 Level 3
- EMC compliance to IEC 60601-1-2 ed. 4
- Protection class I and II
- Operating up to 5000 m altitude
- Ready to meet ErP directive, <0.15 W no load power consumption
- 5 year product warranty













ES 60601-1 IEC 60601-1

The TPP 65A Series of 65 Watt AC/DC power supplies feature a reinforced double I/O isolation system according to latest medical safety standards (60601-1 3rd edition, 2 x MOPP). The earth leakage current is below 75 μA what makes the units suitable for BF (body floating) applications. The excellent efficiency of up to 92% allows a high power density for the standard 2.44" x 3.0" packaging format. The full load operating temperature range is -40°C to $+60^{\circ}\text{C}$ while it goes up to 85°C with 50% load derating. The EMC characteristic is dedicated for applications in industrial and domestic fields. High reliability is provided by the use of industrial quality grade components and an excellent thermal management. It makes the products an ideal solution for medical devices and for demanding safety and space critical applications.

| Models | | | | |
|---------------|-------------------|----------------------------------|---------------------|--------------------|
| Order Code | Output Power max. | Output Voltage nom. (adjustable) | Output Current max. | Efficiency typ. |
| TPP 65-105A-J | 50 W | 5 VDC (4.5 - 5.5 VDC) | 10'000 mA | 90 % |
| TPP 65-112A-J | | 12 VDC (10.8 - 13.2 VDC) | 5'420 mA | 93 % |
| TPP 65-124A-J | 65 W | 24 VDC (21.6 - 26.4 VDC) | 2'710 mA | 94 % |
| TPP 65-148A-J | | 48 VDC (43.2 - 52.8 VDC) | 1'360 mA | 93 % |

Note - Other output models are available on request.



| Input Specifications | | | |
|----------------------|-----------------------------|--|--|
| Input Voltage | - AC Range | 85 - 264 VAC (Full Range) | |
| | - DC Range | 120 - 370 VDC (designed for, no certification) | |
| Input Frequency | | 47 – 63 Hz | |
| Input Current | - Full Load & Vin = 230 VAC | 950 mA max. | |
| | - Full Load & Vin = 115 VAC | 1650 mA max. | |
| Power Consumption | - at no Load | 150 mW max. (Ready to meet ErP directive) | |
| Input Inrush Current | - at 230 VAC | 60 A max. | |
| Input Protection | | T 3.15 A / 250 VAC (Internal Fuse in L & N) | |

| Output Specification | ons | | |
|---------------------------|---------------------------------|---------------|---|
| Output Voltage Adjustmen | t | | ±10% (by trim potentiometer) |
| Voltage Set Accuracy | | | ±1% max. |
| Regulation | - Input Variation (Vmin - Vmax) | | 0.2% max. |
| | - Load Variation (0 - 100%) | | 0.5% max. |
| | | | 0.7% max. (5 VDC model) |
| Ripple and Noise | | 5 VDC model: | 75 mVp-p typ. (with 10 μF X7R) |
| (20 MHz Bandwidth) | | 12 VDC model: | 75 mVp-p typ. (with 10 µF X7R) |
| | | 24 VDC model: | 75 mVp-p typ. (with 1 µF X7R) |
| | | 48 VDC model: | 150 mVp-p typ. (with 0.1 μF X7R) |
| Capacitive Load | | 5 VDC model: | 20'000 μF max. |
| | | 12 VDC model: | 4'520 μF max. |
| | | 24 VDC model: | 1'130 µF max. |
| | | 48 VDC model: | 285 µF max. |
| Minimum Load | | | not required |
| Temperature Coefficient | | | ±0.02 %/K |
| Hold-up Time | - at 115 VAC | | 16 ms min. |
| Start-up Time | - at 230 VAC | | 1'000 ms max. |
| Output Current Limitation | | | 120 - 160% of lout max. |
| Short Circuit Protection | | | Continuous, automatic recovery |
| Overvoltage Protection | | | 125 - 140% of Vout nom. |
| Transient Response | - Response Deviation | | 3% max. (50% to 75% Load Step) |
| | - Response Time | | 600 μs typ. (50% to 75% Load Step) |

| Safety Standards | - Medical Equipment | EN 60601-1 | |
|-----------------------|---------------------------|--|--|
| | | IEC 60601-1 | |
| | | ANSI/AAMI ES 60601-1 | |
| | | 2 x MOPP (Means Of Patient Protection) | |
| | - Certification Documents | www.tracopower.com/overview/tpp65a | |
| Protection Class | | Class I Prepared: Connection to PE | |
| | | Class II Prepared: Reinforced Insulation | |
| Pollution Degree | | PD 2: Office or Laboratory Environments | |
| Over Voltage Category | | OVC II | |

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.



| EMC Specificat | ions | | |
|-----------------------|--|--|--|
| EMC Emission | | EN 60601-1-2 edition 4 (Medical Devices) | |
| | - Conducted Emissions | EN 55011 class B (internal filter) | |
| | | EN 55032 class B (internal filter) | |
| | | FCC Part 18, class B | |
| | - Radiated Emissions | EN 55011 class B (internal filter) | |
| | | EN 55032 class B (internal filter) | |
| | | FCC Part 18, class B | |
| | - Harmonic Current Emissions | EN 61000-3-2, class A | |
| | - Voltage Fluctuations & Flicker | EN 61000-3-3 | |
| EMC Immunity | | EN 60601-1-2 edition 4 (Medical Devices) | |
| | - Electrostatic Discharge | Air: EN 61000-4-2, ±15 kV, perf. criteria A | |
| | | Contact: EN 61000-4-2, ±8 kV, perf. criteria A | |
| | - RF Electromagnetic Field | EN 61000-4-3, 20 V/m, perf. criteria A | |
| | - EFT (Burst) | EN 61000-4-4, ±2 kV, perf. criteria A | |
| | - Surge | L to L: EN 61000-4-5, ±1 kV, perf. criteria A | |
| | - Conducted RF Disturbances | EN 61000-4-6, 20 Vrms, perf. criteria A | |
| | - PF Magnetic Field | EN 61000-4-8, 30 A/m, perf. criteria A | |
| | Voltage Dips & Interruptions | 230 VAC / 50 Hz: EN 61000-4-11 | |
| | | 30%, perf. criteria A, 25 periods | |
| | | >95%, perf. criteria A, 0.5 periods | |
| | | >95%, perf. criteria A, 1 period | |
| | | >95%, perf. criteria B, 250 periods | |
| | | 115 VAC / 60 Hz: EN 61000-4-11 | |
| | | 30%, 25 periods, perf. criteria A | |
| | | >95%, 0.5 periods, perf. criteria A | |
| | | >95%, 1 period, perf. criteria A | |
| | | >95%, 250 periods, perf. criteria B | |

| Relative Humidity | | 95% max. (non condensing) |
|---------------------------------|------------------------------|--|
| Temperature Ranges | - Operating Temperature | -40°C to +85°C |
| | - Storage Temperature | -40°C to +85°C |
| Power Derating | - High Temperature | see application note |
| | | www.tracopower.com/overview/tpp65a |
| | - Low Input Voltage | 4 %/V below 90V |
| Cooling system | | Natural convection (no internal fan, 20 LFM) |
| Altitude during Operation | | 5000 m max. |
| Switching Frequency | | 50 - 140 kHz (PWM) |
| Insulation System | | Reinfoced Insulation |
| Working Voltage (rated) | | 258 VAC |
| solation Test Voltage | - Input to Output, 60 s | 5'657 VDC |
| | - Input to Case or PE, 60 s | 3'535 VDC |
| | - Output to Case or PE, 60 s | 3'535 VDC |
| Isolation Resistance | - Input to Output, 500 VDC | 100 MOhm min. |
| Leakage Current (at 264 VAC) | - Touch Current | 75 μA max. |
| Creepage | | 8 mm min. |
| Clearance | | 8 mm min. |
| Reliability | - Calculated MTBF | 1'500'000 h (acc. to MIL-HDBK-217F) |
| Environment | - Vibration | IEC 60068-2-6 |
| | - Mechanical Shock | IEC 60068-2-27 |
| Connection Type | | JST |
| Weight | | 117 g |
| Environmental Compliance | e - Reach | www.tracopower.com/info/reach-declaration.pd |
| | - RoHS | www.tracopower.com/info/rohs-declaration.pdf |

All specifications valid at nominal input voltage, full load and $\pm 25^{\circ}\text{C}$ after warm-up time unless otherwise stated.




Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tpp65a

Outline Dimensions



TINOINI VILW

Each one of the 4 screw holes can be used as a PE connection for CLASS I application.

Dimensions in inch, () = mm

Outside dimension tolerance: ± 0.02 inch (± 0.5 mm) Hole spacing tolerance: ± 0.01 inch (± 0.25 mm)

| Screw Terminal | | | |
|----------------------------|----------|------|----------|
| Input (CON1) Output (CON1) | | | |
| Pin | Function | Pin* | Function |
| 1 | Line | 1,2 | -Vout |
| 3 | Neutral | 3,4 | +Vout |

*Terminal rated for 7 A max. (at higher current connection has to be split)

CON1: JST series

mates with JST crimp terminal: BVH-21T-P1.1 and terminal housing: VHR-3N $\,$

CON2: JST series

mates with JST crimp terminal: BVH-21T-P1.1 and terminal housing: VHR-4N