

| | | | | | | | | |
|---|---|---|---|--|---|---|--|--|
| Flashprint language | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish | Chinese / English / Arabic / Czech / French / German / Spanish / Japanese / Polish / Turkish |
| Screen language | English | Simple/Traditional Chinese/English/French/German/Japanese/Korean/Arabic/Spanish/Portuguese/Tuikish/Polish/Italian | Simple/Traditional Chinese/English/French/German/Japanese/Korean/Arabic/Spanish/Portuguese/Tuikish/Polish/Italian | Simple/Traditional Chinese/English/French/German/Japanese/Korean/Polish/Espanish | Simple/Traditional Chinese/English/French/German/Japanese/Korean/Arabic/Spanish/Portuguese/Tuikish/Polish/Italian | Simple/Traditional Chinese/English/French/German/Japanese/Korean/Arabic/Spanish/Portuguese/Tuikish/Polish/Italian | Simple/Traditional Chinese/English/French/German/Japanese/Korean/Arabic/Spanish/ | Simple/Traditional Chinese/English/French/German/Japanese |
| Input/Output file type | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: x3g File | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: GX/G File | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: GX/G File | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: GX/G File | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: GX/G File | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: GX/G File | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: GX/G File | Input: 3MF/ STL / OBJ/FPP/BMP/PNG/JPG/JPEG File; Output: GX/G File |
| Printing connection | USB Cable/ SD Card | USB Cable/ U Disk/ Ethernet/WIFI | USB Cable / U Disk / Ethernet/WIFI | USB Cable / SD Card / WIFI | USB Cable/ USB Disk / WIFI | USB Cable / U Disk / WIFI | USB Disk/ WIFI | USB Disk/ WIFI |
| Certification | CE / FCC / RoHS | CE / FCC / RoHS | CE / FCC / RoHS | CE / FCC / RoHS | CE / FCC / RoHS | CE / FCC / RoHS | CE / FCC / RoHS | CE / FCC / RoHS |
| Working temperature | 15-30℃ | 15-30℃ | 15-30℃ | 15-30℃ | 20~30℃ | 20~30℃ | 15-30℃ | 15-30℃ |
| Compatible operating system | Win xp/Vista/7/8/10、Mac OS、Linux | Win xp/Vista/7/8/10、Mac OS、Linux | Win xp/Vista/7/8/10、Mac OS、Linux | Win xp/Vista/7/8/10、Mac OS、Linux | Win xp/Vista/7/8/10、Mac OS、Linux | Win xp/Vista/7/8/10、Mac OS、Linux | Win xp/Vista/7/8/10、Mac OS、Linux | Win xp/Vista/7/8/10、Mac OS、Linux |
| Compatible slicing software | simplify3D 3.0 version、ReplicatorG、Makerware (Direct Use) Slic3r, Skeinforge, Cura (Need to set up) | Slic3r, Skeinforge, Cura (Need to set up) | Slic3r, Skeinforge, Cura (Need to set up) | Slic3r, Skeinforge, Cura (Need to set up) | Slic3r, Skeinforge, Cura (Need to set up) | Slic3r, Skeinforge, Cura (Need to set up) | Slic3r, Skeinforge, Cura (Need to set up) | Slic3r, Skeinforge (Need to set up) |
| Heating bed | √ | √ | √ | √ | × | × | √ | √ |
| Close design | √ | √ | √ | √ | √ | √ | √ | √ |
| Auxiliary leveling | × | √ | √ | × | √ | √ | × | √ |
| Filament running out reminding | × | √ | √ | × | √ | √ | √ | √ |
| Replaceable print bed | × | × | × | × | √ | √ | √ | √ |
| Ultra silence design | × | × | × | × | √ | √ | √ | × |
| Continue last printing when power off | × | √ | √ | √ | × | × | × | × |
| Intelligent door sensor | × | × | × | × | √ | √ | × | √ |
| Touch LCD screen | × | √ | √ | √ | √ | √ | √ | √ |
| Constant temperature and circumfluence system | × | × | × | √ | × | × | × | × |
| Remote camera watching | × | × | √ | √ | × | × | √ | √ |
| Wireless WIFI | × | √ | √ | √ | √ | √ | √ | √ |
| Ethernet | × | √ | √ | × | × | × | √ | √ |
| USB stick Interface | × | √ | √ | × | √ | √ | √ | √ |

| | | | | | | | | |
|-----------------------|---|---|---|---|---|---|---|---|
| Air filter net | × | × | √ | × | × | √ | × | √ |
| Magnetic Printing bed | × | × | × | × | × | √ | × | × |
| Cloud | × | √ | √ | × | √ | √ | √ | √ |