

PT-E300VP

brother  
at your side




## Industrial Labelling Machine

With dedicated functions for engineering label applications, easily create durable labels for faceplates, cables, consumer units and other electrical and datacom installations.

- Prints on new **heat shrink** tube cartridges
- Prints 6, 9, 12 & 18mm labels
- Industry standard barcode compatible
- Large backlit graphic display
- Dedicated function keys to easily create labels
- Includes tape cassette, Li-ion Battery, AC adapter, wrist strap and carry case
- Over 300 electrical datacom symbols.







**The P-touch E300VP can also use the new Heat shrink tube tape (HSe) in addition to the durable TZE laminated tapes.**

### **P-touch laminated labels – designed to last**

Brother P-touch laminated TZe tapes consist of seven layers of materials, resulting in a thin, extremely strong label. Characters are formed with a thermal transfer ink and sandwiched between two protective layers of PET (polyester film). The result is a virtually indestructible label that can withstand even the harshest conditions.

# P-touch E300VP

The P-touch E300VP is an indispensable tool for all electricians and datacom installers. It comes complete with a lithium-ion rechargeable battery and AC adapter, all housed in a durable carry case. The large backlit graphic LCD, standard QWERTY style keyboard and specialised functions have been developed to make common industrial labelling tasks quick and easy. Leave a professional impression by creating high quality labels for your installations.



### Prints labels 6 to 18mm in width

Print labels in various widths from 6 to 18mm to suit any space.



### Large backlit graphic LCD

Easily view symbols and preview your label before printing.



### Face plate

Label socket outlets, network points and telephone extension faceplates for quick identification.



### Patch Panel

Create perfectly sized port identification labels.



### Cable wrap ; Cable flag

Identify cables quickly with easy-to-read labels.



### Sequential numbering

Print labels containing a sequence of numbers or letters.



### 9 barcode protocols

Include barcodes for added security and safety.



### 384 built-in symbols

Includes common electrical, datacom, AV, security and safety symbols.



Laminated



Temperature Resistant



Water Resistant



Fade Resistant



Abrasion Resistant



Chemical Resistant



Easy Peel



Strong Adhesion

# PT-E300VP

PT-E300VP is an industrial labelling machine for the electrical and datacom industry. Fast print speed of 30mm/sec. Prints on durable TZe laminated labels and heat shrink tube tape (HSe). It comes with a flexible ID tape, Li-ion battery, A/C Adapter and a tough carry case. Create professional, durable, laminated labels for cables, faceplates, consumer units and other electrical and datacom installations with its dedicated function keys for easy access.




### Heat-shrink tube

Shrinks and grips cable when heat is applied.



### Flexible-ID Tape

Use on curved surfaces, sharp bends or cylindrical surfaces.



### Strong Adhesive Tape

Use on uneven, rough and textured surfaces.

## Technical Specifications

### Hardware

Housing dimensions	133 (w) x 220 (h) x 69 (d)
Housing weight	740g
Tape size/type	TZe tape: 6, 9, 12, 18mm
Print resolution	180 dpi
Max. print height	15.8mm
Max. print speed	20mm / sec
Cutter type	Manual: Cutter blade
Keyboard type	QWERTY with numeric keypad
Number of keys	64
LCD display	15 characters x 3 line graphic
LCD backlight	Yes
LCD size	67mm x 40mm
Print preview	Yes
Text buffer	Max. 200 chrs
Label memory	50 memory locations with up to 2,400 characters total
Power	Li-ion battery (supplied) AC adapter (supplied) 6 x AA alkaline batteries (not supplied)

### Items Included in value pack

PT-E300 labelling machine  
Lithium-ion battery  
AC adapter  
9mm black on white strong adhesive  
Label cassette  
User guide  
Wrist strap  
Carry case

### Built-in software

Built-in fonts	7
Built-in symbols	384
Character sizes	7: (6, 9, 12, 18, 24, 36, 42 pt)
Character widths	4: (x $\frac{1}{2}$ , x $\frac{2}{3}$ , normal, x2)
Font styles	9
Frames	7
Underline	Yes
Max. number of lines	5
Horizontal alignment	Automatic length labels: left aligned Pre-set label length: centre aligned
Tape length setting	Yes (25-300mm)
Tape margin setting	Narrow, half, full, chain print
Tab function	Yes
Specialist labelling functions	Cable wrap, cable flag, faceplate, sequential numbering, patch panel, punch block
Automatic numbering	Yes
Mirror printing	No
Vertical printing	Yes
Barcode	Yes: 9 kinds
Copy (repeat) printing	Yes: (1-9)
Print preview	Yes: (graphic preview)
Auto power off	Yes
Unit change	Yes: (inch/mm)

### Supplies

Tape type; Tape widths	TZe tape cassettes; 6, 9, 12, 18mm HSe tube cassettes; 5.8, 8.8, 11.7 and 17.7mm
------------------------	---

P-touch

TZe  
TAPE

Label  
brother

HSe  
TUBE

brother  
at your side

### Brother International South Africa

96 Sovereign Drive, Route 21 Corporate Park, Irene  
Tel: +27 (0) 12 - 345 5332 Fax: +27 (0) 12 - 345 3886

www.brother.co.za <http://solutions.brother.com>



Working with you for a better environment  
[www.brotherearth.com](http://www.brotherearth.com)



Japanese  
Excellence  
For Over 100 Years