

MAX540H245STR

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Stackable interlocking system
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer

Latches: nylon

Pins: nylon + 30% fiberglass

O-ring: polymer

Wheels: Nylon + Polyurethane

Pin of the wheels: Stainless Steel

COLOURS: Black

EXTERNAL DIMENSIONS: 604 x 473 x H283 mm (23.78 x 18.62 x H11.14 inch)

INTERNAL DIMENSIONS: 538 x 405 x H245 mm (21.18 x 15.94 x H9.64 inch)

LID-BOTTOM DEPTH: 50 + 195 mm (1.97 + 7.68 inch)

WEIGHT WITH FOAM: 7.70 kg – 16.98 lbs.

CAPACITY: 25kg – 55 lbs.

DIAMETER OF THE WHEELS: 60mm – 2.362 inch

CARTON DIMENSIONS: 620x500x290mm – 24.41x19.69x11.42 inch

PCS PER CARTON: 1

WEIGHT OF THE FULL CARTON WITH FOAMS: 8.86kg – 19.53 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: wheels, extendable handle, IP67

CUSTOMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foams, padded dividers, lid organizer, backpack

