


IRF9952QPbF

HEXFET® Power MOSFET

- Advanced Process Technology
- Ultra Low On-Resistance
- Dual N and P Channel MOSFET
- Surface Mount
- Available in Tape & Reel
- 150°C Operating Temperature
- Automotive [Q101] Qualified
- Lead-Free




	N-Ch	P-Ch
V _{DSS}	30V	-30V
R _{DS(on)}	0.10Ω	0.25Ω

Description

Specifically designed for Automotive applications, these HEXFET® Power MOSFET's in a Dual SO-8 package utilize the lastest processing techniques to achieve extremely low on-resistance per silicon area. Additional features of these Automotive qualified HEXFET Power MOSFET's are a 150°C junction operating temperature, fast switching speed and improved repetitive avalanche rating. These benefits combine to make this design an extremely efficient and reliable device for use in Automotive applications and a wide variety of other applications.

The efficient SO-8 package provides enhanced thermal characteristics and dual MOSFET die capability making it ideal in a variety of power applications. This dual, surface mount SO-8 can dramatically reduce board space and is also available in Tape & Reel.



	Symbol	Maximum		Units
		N-Channel	P-Channel	
Drain-Source Voltage	V _{DS}	30		V
Gate-Source Voltage	V _{GS}	± 20		
Continuous Drain Current ^⑤	I _D	3.5	-2.3	A
		2.8	-1.8	
Pulsed Drain Current	I _{DM}	16	-10	
Continuous Source Current (Diode Conduction)	I _S	1.7	-1.3	
Maximum Power Dissipation ^⑤	P _D	2.0		W
		1.3		
Single Pulse Avalanche Energy	E _{AS}	44	57	mJ
Avalanche Current	I _{AR}	2.0	-1.3	A
Repetitive Avalanche Energy	E _{AR}	0.25		mJ
Peak Diode Recovery dv/dt ^②	dv/dt	5.0	-5.0	V/ns
Junction and Storage Temperature Range	T _J , T _{STG}	-55 to + 150		°C

Thermal Resistance Ratings

Parameter	Symbol	Limit	Units
Maximum Junction-to-Ambient ^⑥	R _{θJA}	62.5	°C/W

IRF9952QPbF

International
Rectifier

Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

	Parameter		Min.	Typ.	Max.	Units	Conditions
$V_{(\text{BR})\text{DSS}}$	Drain-to-Source Breakdown Voltage	N-Ch	30	—	—	V	$V_{GS} = 0V, I_D = 250\mu\text{A}$
		P-Ch	-30	—	—		$V_{GS} = 0V, I_D = -250\mu\text{A}$
$\Delta V_{(\text{BR})\text{DSS}}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	N-Ch	—	0.015	—	$\text{V}/^\circ\text{C}$	Reference to 25°C , $I_D = 1\text{mA}$
		P-Ch	—	0.015	—		Reference to 25°C , $I_D = -1\text{mA}$
$R_{DS(\text{ON})}$	Static Drain-to-Source On-Resistance	N-Ch	—	0.08	0.10	Ω	$V_{GS} = 10V, I_D = 2.2\text{A}$ ④
		—	—	0.12	0.15		$V_{GS} = 4.5V, I_D = 1.0\text{A}$ ④
		—	—	0.165	0.250		$V_{GS} = -10V, I_D = -1.0\text{A}$ ④
		P-Ch	—	0.290	0.400		$V_{GS} = -4.5V, I_D = -0.50\text{A}$ ④
$V_{GS(\text{th})}$	Gate Threshold Voltage	N-Ch	1.0	—	—	V	$V_{DS} = V_{GS}, I_D = 250\mu\text{A}$
		P-Ch	-1.0	—	—		$V_{DS} = V_{GS}, I_D = -250\mu\text{A}$
g_{fs}	Forward Transconductance	N-Ch	—	12	—	S	$V_{DS} = 15V, I_D = 3.5\text{A}$ ④
		P-Ch	—	2.4	—		$V_{DS} = -15V, I_D = -2.3\text{A}$ ④
I_{DSS}	Drain-to-Source Leakage Current	N-Ch	—	—	2.0	μA	$V_{DS} = 24V, V_{GS} = 0V$
		P-Ch	—	—	-2.0		$V_{DS} = -24V, V_{GS} = 0V$
		N-Ch	—	—	25		$V_{DS} = 24V, V_{GS} = 0V, T_J = 125^\circ\text{C}$
		P-Ch	—	—	-25		$V_{DS} = -24V, V_{GS} = 0V, T_J = 125^\circ\text{C}$
I_{GSS}	Gate-to-Source Forward Leakage	N-P	—	—	± 100	nA	$V_{GS} = \pm 20V$
Q_g	Total Gate Charge	N-Ch	—	6.9	14	nC	N-Channel $I_D = 1.8\text{A}, V_{DS} = 10V, V_{GS} = 10V$ ④
		P-Ch	—	6.1	12		P-Channel $I_D = -2.3\text{A}, V_{DS} = -10V, V_{GS} = -10V$
Q_{gs}	Gate-to-Source Charge	N-Ch	—	1.0	2.0	nC	
		P-Ch	—	1.7	3.4		
Q_{gd}	Gate-to-Drain ("Miller") Charge	N-Ch	—	1.8	3.5	nC	
		P-Ch	—	1.1	2.2		
$t_{d(on)}$	Turn-On Delay Time	N-Ch	—	6.2	12	ns	N-Channel $V_{DD} = 10V, I_D = 1.0\text{A}, R_G = 6.0\Omega, R_D = 10\Omega$ ④
		P-Ch	—	9.7	19		
t_r	Rise Time	N-Ch	—	8.8	18	ns	P-Channel $V_{DD} = -10V, I_D = -1.0\text{A}, R_G = 6.0\Omega, R_D = 10\Omega$ ④
		P-Ch	—	14	28		
$t_{d(off)}$	Turn-Off Delay Time	N-Ch	—	13	26	ns	
		P-Ch	—	20	40		
t_f	Fall Time	N-Ch	—	3.0	6.0	ns	
		P-Ch	—	6.9	14		
C_{iss}	Input Capacitance	N-Ch	—	190	—	pF	N-Channel $V_{GS} = 0V, V_{DS} = 15V, f = 1.0\text{MHz}$
		P-Ch	—	190	—		
C_{oss}	Output Capacitance	N-Ch	—	120	—	pF	P-Channel $V_{GS} = 0V, V_{DS} = -15V, f = 1.0\text{MHz}$
		P-Ch	—	110	—		
C_{rss}	Reverse Transfer Capacitance	N-Ch	—	61	—	pF	
		P-Ch	—	54	—		

Source-Drain Ratings and Characteristics

	Parameter		Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	N-Ch	—	—	1.7	A	
		P-Ch	—	—	-1.3		
I_{SM}	Pulsed Source Current (Body Diode) ④	N-Ch	—	—	16	A	
		P-Ch	—	—	16		
V_{SD}	Diode Forward Voltage	N-Ch	—	0.82	1.2	V	$T_J = 25^\circ\text{C}, I_S = 1.25\text{A}, V_{GS} = 0V$ ④
		P-Ch	—	-0.82	-1.2		$T_J = 25^\circ\text{C}, I_S = -1.25\text{A}, V_{GS} = 0V$ ④
t_{rr}	Reverse Recovery Time	N-Ch	—	27	53	ns	N-Channel $T_J = 25^\circ\text{C}, I_F = 1.25\text{A}, di/dt = 100\text{A}/\mu\text{s}$
		P-Ch	—	27	54		
Q_{rr}	Reverse Recovery Charge	N-Ch	—	28	57	nC	P-Channel $T_J = 25^\circ\text{C}, I_F = -1.25\text{A}, di/dt = 100\text{A}/\mu\text{s}$ ④
		P-Ch	—	31	62		

Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature. (See fig. 23)
- ② N-Channel $I_{SD} \leq 2.0\text{A}$, $di/dt \leq 100\text{A}/\mu\text{s}$, $V_{DD} \leq V_{(\text{BR})\text{DSS}}$, $T_J \leq 150^\circ\text{C}$
P-Channel $I_{SD} \leq -1.3\text{A}$, $di/dt \leq 84\text{A}/\mu\text{s}$, $V_{DD} \leq V_{(\text{BR})\text{DSS}}$, $T_J \leq 150^\circ\text{C}$
- ③ N-Channel Starting $T_J = 25^\circ\text{C}$, $L = 22\text{mH}$ $R_G = 25\Omega$, $I_{AS} = 2.0\text{A}$. (See Figure 12)
P-Channel Starting $T_J = 25^\circ\text{C}$, $L = 67\text{mH}$ $R_G = 25\Omega$, $I_{AS} = -1.3\text{A}$.
- ④ Pulse width $\leq 300\mu\text{s}$; duty cycle $\leq 2\%$.
- ⑤ Surface mounted on FR-4 board, $t \leq 10\text{sec}$.




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. Typical Transfer Characteristics




Fig 4. Typical Source-Drain Diode Forward Voltage

IRF9952QPbF

N-Channel

International
Rectifier




Fig 5. Normalized On-Resistance Vs. Temperature




Fig 6. Typical On-Resistance Vs. Drain Current




Fig 7. Typical On-Resistance Vs. Gate Voltage




Fig 8. Maximum Avalanche Energy Vs. Drain Current




Fig 9. Typical Capacitance Vs.
Drain-to-Source Voltage




Fig 10. Typical Gate Charge Vs.
Gate-to-Source Voltage




Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient

IRF9952QPbF

P-Channel

International
Rectifier




Fig 12. Typical Output Characteristics




Fig 13. Typical Output Characteristics




Fig 14. Typical Transfer Characteristics




Fig 15. Typical Source-Drain Diode Forward Voltage




Fig 16. Normalized On-Resistance Vs. Temperature




Fig 17. Typical On-Resistance Vs. Drain Current




Fig 18. Typical On-Resistance Vs. Gate Voltage




Fig 19. Maximum Avalanche Energy Vs. Drain Current

IRF9952QPbF

P-Channel

International
Rectifier




Fig 20. Typical Capacitance Vs.
Drain-to-Source Voltage




Fig 21. Typical Gate Charge Vs.
Gate-to-Source Voltage





Fig 22. Maximum Effective Transient Thermal Impedance, Junction-to-Ambient
www.irf.com

International
IR Rectifier


IRF9952QPbF

SO-8 Package Outline


Dimensions are shown in millimeters (inches)



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	.0532	.0688	1.35	1.75
A1	.0040	.0098	0.10	0.25
b	.013	.020	0.33	0.51
c	.0075	.0098	0.19	0.25
D	.189	.1968	4.80	5.00
E	.1497	.1574	3.80	4.00
e	.050	BASIC	1.27	BASIC
e1	.025	BASIC	0.635	BASIC
H	.2284	.2440	5.80	6.20
K	.0099	.0196	0.25	0.50
L	.016	.050	0.40	1.27
y	0°	8°	0°	8°




FOOTPRINT



SO-8 Part Marking

EXAMPLE: THIS IS AN IRF7101 (MOSFET)




Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>
www.irf.com

IRF9952QPbF

International
IR Rectifier


SO-8 Tape and Reel

Dimensions are shown in millimeters (inches)



NOTES:

1. CONTROLLING DIMENSION : MILLIMETER.
2. ALL DIMENSIONS ARE SHOWN IN MILLIMETERS(INCHES).
3. OUTLINE CONFORMS TO EIA-481 & EIA-541.



NOTES :

1. CONTROLLING DIMENSION : MILLIMETER.
2. OUTLINE CONFORMS TO EIA-481 & EIA-541.

Note: For the most current drawing please refer to IR website at <http://www.irf.com/package/>

Data and specifications subject to change without notice.
This product has been designed and qualified for the Automotive [Q101] market.
Qualification Standards can be found on IR's Web site.

International
IR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7903

Visit us at www.irf.com for sales contact information.07/2007