

# ZCE64

limit switch head ZCE - side steel roller plunger  
horizontal



## Main

|                           |   |
|---------------------------|---|
| Range of product          | OsiSense XC   |
| Series name               | Standard format   |
| Product or component type | Limit switch head   |
| Device short name         | ZCE   |
| Head type                 | Plunger head  |
| Product compatibility     | XCKT<br>XCKP<br>XCKD<br>XCMD  |
| Associated body           | ZCMD21L5<br>ZCMD81L5<br>ZCMD25L2<br>ZCP29<br>ZCT28P16<br>ZCP26<br>ZCP21M12<br>ZCMD39L1<br>ZCMD61C12<br>ZCMD25L1<br>ZCD29<br>ZCD29M12<br>ZCP28<br>ZCT25P16<br>ZCMD21L08R12<br>ZCMD39L5<br>ZCMD61M12<br>ZCT27G11<br>ZCMD81L2<br>ZCP29M12<br>ZCMD37L1<br>ZCMD41L5<br>ZCT26G11<br>ZCP27<br>ZCT26P16<br>ZCMD29C12<br>ZCT21G11<br>ZCMD21M12 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCMD39L2  
 ZCT28G11  
 ZCD31  
 ZCP37  
 ZCD26  
 ZCD35  
 ZCMD29L1  
 ZCD28  
 ZCD27  
 ZCT21N12  
 ZCT27N12  
 ZCT28N12  
 ZCMD25L5  
 ZCD37  
 ZCD39  
 ZCMD81L1  
 ZCMD37L5  
 ZCMD21C12  
 ZCT25N12  
 ZCT27P16  
 ZCMD41L1  
 ZCP25  
 ZCT25G11  
 ZCP39  
 ZCP31  
 ZCT21P16  
 ZCMD21L2  
 ZCMD29L5  
 ZCP21  
 ZCT26N12  
 ZCMD37L2  
 ZCD21  
 ZCP35  
 ZCMD41L2  
 ZCMD21L08U78  
 ZCD25  
 ZCMD29L2  
 ZCD21M12  
 ZCMD21L1  
 ZCMD69C12

|                            |  |
|----------------------------|--|
| Movement of operating head | Linear   |
| Type of operator           | Side roller plunger spring return metal (with horizontal roller) |
| Type of approach           | Lateral approach 2 directions                                    |

### Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | Without    |

### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -25...70 °C          |
| Ambient air temperature for storage   | -40...70 °C          |
| Environmental characteristic          | Standard environment |

### Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 0851 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product end of life instructions | Need no specific recycling operations   |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|