



# Energizer Industrial<sup>®</sup> Vision HD+ Focus Headlight

The Energizer<sup>®</sup> Industrial Vision HD+ Focus headlight is another innovative headlight solution within the Energizer<sup>®</sup> premium headlight line. With the latest LED technology, users get an extraordinarily bright, lightweight hands-free solution with ample run time. Custom optics offer exceptional direct and peripheral vision, making the Energizer<sup>®</sup> Vision HD+ Focus a perfect light for home, work and outdoor activities. Featuring patented digital focus, users can easily broaden or narrow their field of vision with a simple button press. Memory Recall allows users to quickly access their favorite focus setting the next time the light is activated. With an adjustable head strap, water-resistant design and pivoting head to direct light exactly as needed, Energizer<sup>®</sup> continues to deliver innovative lighting solutions.

## Design Benefits


- ✓ Patented Digital Focus allows users to broaden or narrow the light beam
- ✓ Red LED mode allows users to preserve night vision
- ✓ Silicone beading on head strap for extra grip
- ✓ Pivoting head to direct light where needed
- ✓ IPX4 water resistant and shatterproof lens construction

## Performance Benefits

- ✓ Memory Recall feature allows users to quickly access their favorite focus setting the next time the light is activated
- ✓ Up to 4X brighter than standard LED technology
- ✓ Custom optics deliver exceptional direct and peripheral vision

## Light and Power Source

- ✓ Features LED technology
- ✓ Operates on 3AAA batteries
  - ✓ (Includes 3AAA Energizer MAX<sup>®</sup> batteries)



5 Operating Modes + Digital Focus Feature					
Mode	Lumens	Runtime	Beam Distance	Impact Resistant	Water Resistant
Red	-	18hrs	-	1m	IPX4
White - High	315	6hrs	85m	1m	IPX4
White - Low	20	50hrs	-	1m	IPX4
Spot - High	180	12hrs	-	1m	IPX4
Flood - High	100	20hrs	-	1m	IPX4