


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0740579009**

Status: **Active**

Overview: VHDM Backplane Connector Systems

Description: VHDM Single-Ended Board-to-Board Backplane Header, 2.00mm Pitch, Vertical, 6-Rows, Open Signal Module, 60 Circuits, 10 Columns, Pin Length 5.15mm, 1.27µm Gold (Au) Plating, Series:74074 Enables designers to create custom loaded connectors utilizing standard pin lengths 4.25, 4.75, 5.15 and 6.25mm



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Packaging Specification PK-74057-003 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family	Backplane Connectors
Series	74057
Application	Backplane
Application Tooling Documents	TM-622010999
Comments	Backplane Header Module, Signal, Open, Backplane Header Module, Signal, Open
Component Type	PCB Header
Overview	VHDM Backplane Connector Systems
Product Name	VHDM
UPC	884982749191

Physical

Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	Beryllium Copper, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.298/g
Number of Columns	10
Number of Pairs	Open Pin Field
Number of Rows	6
Orientation	Vertical
PC Tail Length	2.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.80mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	1.270µm
Plating min - Termination	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	105°C

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[74057 Series](#)

Mates With

[74030](#) VHDM Board-to-Board Daughtercard Receptacle

Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 2.0A
Data Rate 3.125 Gbps
Shield Type Ground Plane Shield
Shielded Yes
Voltage - Maximum 120V AC (RMS)/DC

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification PK-74057-003
Sales Drawing SD-74057-002

This document was generated on 07/03/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION