

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0782321001**
Status: **Active**
Overview: GbX I-Trac Backplane Connector System
Description: GbX I-Trac Vertical Receptacle, Power Module, 2 Blades, 80 Amps, Lead-Free

Documents:

[3D Model](#) [Packaging Specification PK-78232-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-78231-006-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General


Product Family Backplane Connectors
 Series 78232
 Application Backplane, Midplane
 Component Type Power Receptacle
 Overview GbX I-Trac Backplane Connector System
 Product Name GbX I-Trac
 UPC 822350856553

Physical

Circuits (Loaded) 4
 Circuits (maximum) 4
 Circuits Detail 80 Amps (40/Split Blade)
 Color - Resin Black
 Durability (mating cycles max) 100
 First Mate / Last Break No
 Flammability 94V-0
 Guide to Mating Part No
 Keying to Mating Part None
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 2.676/g
 Number of Columns 1
 Number of Pairs 6
 Number of Rows 2
 Orientation Vertical
 PC Tail Length 2.41mm
 PCB Locator No
 PCB Retention Yes
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 2.00mm, 7.40mm
 Pitch - Termination Interface 2.00mm, 7.40mm
 Polarized to PCB No
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -20° to +85°C
 Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 80.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

78232 Series

Mates With

78234 GbX I-Trac Right Angle Header,
 Power Module

Use With

75705 GbX I-Trac Vertical, 11 Row Header
 Module

Data Rate	12.0 Gbps
Shield Type	N/A
Shielded	No
Voltage - Maximum	250V DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-78232-001
Product Specification	PS-78231-006-001
Sales Drawing	SD-78232-011

This document was generated on 05/15/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION