



**8442 Non-Paired - High-Conductivity Copper Speaker Cable Twisted Jacketed Con**

 	<p>For more information please call <b>1-800-Belden1</b></p> <p><u>See Put-ups and Colors</u></p>
--	---

**Description:**

22 AWG stranded (7x30) tinned copper conductors, PVC insulation, twisted pair, chrome PVC jacket.

**PHYSICAL CHARACTERISTICS:**

**CONDUCTOR:**

Number of Conductors	2
Total Number of Conductors	2
AWG	22
Stranding	7x30
Conductor Material	TC - Tinned Copper

**INSULATION:**

Insulation Material	PVC - Polyvinyl Chloride
Nom. Insulation Wall Thickness	.015 in.

**OVERALL CABLING:**

Overall Cabling Lay Length	1.5 in.
----------------------------	---------

Overall Cabling Color Code Chart :

Number	Color	Number	Color
1	Black	2	Red

**OUTER SHIELD:**

Outer Shield Material	Unshielded
-----------------------	------------

**OUTER JACKET:**

Outer Jacket Material	PVC - Polyvinyl Chloride
Outer Jacket Nominal Wall Thickness	.025 in.

**OVERALL NOMINAL DIAMETER:**

Overall Nominal Diameter	.170 in.
--------------------------	----------

**MECHANICAL CHARACTERISTICS:**

Operating Temperature Range	-20°C To +60°C
Bulk Cable Weight	13 lbs/1000 ft.
Max. Recommended Pulling Tension	18 lbs.



## 8442 Non-Paired - High-Conductivity Copper Speaker Cable Twisted Jacketed Con

Min. Bend Radius (Install)	1.65 in.
----------------------------	----------

### APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

#### APPLICABLE STANDARDS:

NEC/(UL) Specification	CMG
CEC/C(UL) Specification	CMG
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005

#### FLAME TEST:

C(UL) Flame Test	FT4
------------------	-----

#### PLENUM/NON-PLENUM:

Plenum (Y/N)	N
Plenum Number	88442, 82442

#### ELECTRICAL CHARACTERISTICS:

Nom. Inductance	.2 $\mu$ H/ft
Nom. Capacitance Conductor to Conductor @ 1 KHz	30 pF/ft
Nom. Conductor DC Resistance @ 20 Deg. C	15.6 Ohms/1000 ft
Max. Operating Voltage - UL	300 V RMS
Max. Recommended Current	2.9 Amps per conductor @ 25°C

#### PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
8442 060100	2 #22 PVC PVC	100	2.4	CHROME	
8442 0601000	2 #22 PVC PVC	1000	15	CHROME	C
8442 06010000	2 #22 PVC PVC	10000	150	CHROME	C Y
8442 060500	2 #22 PVC PVC	500	7.5	CHROME	
8442 060U1000	2 #22 PVC PVC	U1000	15	CHROME	
8442 060U500	2 #22 PVC PVC	U500	8	CHROME	

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN. MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Revision Number: 1      Revision Date: 08-17-2005



## **8442 Non-Paired - High-Conductivity Copper Speaker Cable Twisted Jacketed Con**

---

© 2006 Belden Wire & Cable Company  
All Rights Reserved.

Although Belden Electronics Division ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden CDT Electronics Division believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs. (San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003); Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden CDT Electronics Division declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.