



Main

| | |
|--|----------------------|
| Range of product | OsiSense XU |
| Series name | Application assembly |
| Specific application of photoelectric detector | Object |
| Sensor name | XUD |

Complementary

| | |
|---------------------------|---|
| Electronic sensor type | Photo-electric sensor |
| Sensor design | Fiber design |
| Enclosure material | PBT |
| Wiring technique | 3-wire |
| Supply circuit type | DC |
| Type of output signal | Discrete |
| Output type | Solid state |
| Discrete output function | 1 NO or 1 NC programmable |
| Discrete output type | NPN |
| Electrical connection | 1 male connector M8, 4 pins |
| Cable material | PVC |
| Status LED | 1 LED red instability 1 LED yellow output state |
| [Us] rated supply voltage | 12...24 V DC reverse polarity protection |
| Supply voltage limits | 10.8...26.4 V DC |
| Current consumption | <= 50 mA (no-load) |
| Switching capacity in mA | <= 100 mA overload protection <= 100 mA short-circuit protection |
| Voltage drop | <= 1 V closed |
| Switching frequency | <= 1 kHz |
| Add on output | Without |
| Delay first up | < 120 ms |
| Delay response | < 0.5 ms |
| Delay recovery | < 0.5 ms |
| Product compatibility | Glass or plastic fibre optics 1 mm or 2.2 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------|--|
| Setting-up | Sensitivity adjustment with teach mode |
| Lens material | PMMA |
| Depth | 10 mm |
| Height | 65 mm |
| Width | 40 mm |
| Product weight | 0.04 kg |

Environment

| | |
|---------------------------------------|---|
| Emission | Red |
| Interference protection | Without |
| Product certifications | CE cULus |
| IP degree of protection | IP64 IEC 529 optic fiber Ø 1 mm IP65 IEC 529 optic fiber Ø 2 mm |
| Ambient air temperature for operation | -10...55 °C |
| Ambient air temperature for storage | -30...70 °C |
| Vibration resistance | 7 gn 10...55 Hz) IEC 60068-2-6 +/-0.5 mm 10...55 Hz) IEC 60068-2-6 |
| Shock resistance | 30 gn (duration = 11 ms) conforming to IEC 60068-2-27 |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 0623 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
|------------------------|---|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|