

Digital Multimeters



72-2605



72-10405



72-2610



72-10410



72-10415



Digital Multimeters



Features

- LCD backlight
- Analog Bar Graph
- Manual Function Select & Auto Ranging
- Auto Power Off
- Low Battery Indication: $\leq 7.5V$
- Diode Test
- Continuity Buzzer
- MAX / MIN / Relative Modes
- Data Hold
- Duty Cycle: 0.1% ~ 99.9%
- Input Protection
- Input Impedance for DC Voltage: 10M Ω

General Characteristics

Safety Rating : CAT III 1000V, CAT IV 600V
 Power : 9V Battery (6F22)
 LCD Size : 65mm \times 43mm
 Colour : Orange and Grey
 Weight : 370g
 Dimension (H \times W \times L) : 180mm \times 87mm \times 47mm

Electrical Specifications

Parameters	72-2605	72-10405	72-2610	72-10410	72-10415
DC Voltage (V)	400mV/4V/40V/400V/1000V $\pm(0.5\% + 1 \text{ digit})$	40mV/400mV/4V/40V/400V/1000V $\pm(0.5\% + 1 \text{ digit})$	60mV/600mV/6V/60V/600V/1000V $\pm(0.5\% + 1 \text{ digit})$		220mV/2.2V/22V/220V/1000V $\pm(0.1\% + 2 \text{ digits})$
AC Voltage (V)	400mV/4V/40V/400V/ 750V $\pm(1\% + 3 \text{ digits})$	40mV/400mV/4V/40V/400V/750V $\pm(1\% + 3 \text{ digits})$	60mV/600mV/6V/60V/600V/750V $\pm(1\% + 3 \text{ digits})$		220mV/2.2V/22V/220V/750V $\pm(0.8\% + 10 \text{ digits})$
DC Current (A)	400 μ A/4000 μ A/40mA/400mA/4A/10A $\pm(1\% + 2 \text{ digits})$		600 μ A/6000 μ A/60mA/600mA/6A/10A $\pm(1\% + 3 \text{ digits})$		200 μ A/2200 μ A/22mA/220mA/ 2.2A/10A $\pm(0.5\% + 10 \text{ digits})$
AC Current (A)	400 μ A/4000 μ A/40mA/400mA/4A/10A $\pm(1.2\% + 5 \text{ digits})$		600 μ A/6000 μ A/60mA/600mA/6A/10A $\pm(1.2\% + 5 \text{ digits})$		200 μ A/2200 μ A/22mA/220mA/ 2.2A/10A $\pm(0.8\% + 10 \text{ digits})$
Resistance (Ω)	400 Ω /4k Ω /40k Ω /400k Ω /4M Ω /40M Ω $\pm(1\% + 2 \text{ digits})$		600 Ω /6k Ω /60k Ω /600k Ω /6M Ω /60M Ω $\pm(1\% + 2 \text{ digits})$		220 Ω /2.2k Ω /22k Ω /220k Ω /2.2M Ω / 22M Ω $\pm(0.5\% + 10 \text{ digits})$
Capacitance (F)	40nF/400nF/4 μ F/40 μ F/400 μ F/4000 μ F $\pm(3\% + 5 \text{ digits})$		40nF/400nF/4 μ F/40 μ F/400 μ F/4000 μ F $\pm(3\% + 5 \text{ digits})$		22nF/220nF/2.2 μ F/22 μ F/220 μ F/2.2mF/ 22mF/220mF $\pm(3\% + 5 \text{ digits})$
Frequency (Hz)	10Hz to 10MHz $\pm(0.1\% + 4 \text{ digits})$	10Hz to 10MHz $\pm(0.1\% + 4 \text{ digits})$	10Hz to 10MHz $\pm(0.1\% + 4 \text{ digits})$	10Hz to 10MHz $\pm(0.1\% + 4 \text{ digits})$	10Hz to 220MHz $\pm(0.01\% + 5 \text{ digits})$
Temperature ($^{\circ}$ C)	-	-40 $^{\circ}$ C to 1000 $^{\circ}$ C $\pm(1.2\% + 3 \text{ digits})$	-40 $^{\circ}$ C to 1000 $^{\circ}$ C $\pm(1.2\% + 3 \text{ digits})$	-	-
Temperature ($^{\circ}$ F)	-	-40 $^{\circ}$ F to 1832 $^{\circ}$ F $\pm(1.2\% + 4 \text{ digits})$	-40 $^{\circ}$ F to 1832 $^{\circ}$ F $\pm(1.2\% + 4 \text{ digits})$	-	-
Display Count	4000	4000	6000	6000	22000
True RMS	-	-	-	Yes	Yes
Bandwidth (Hz)	45Hz - 400Hz	45Hz - 400Hz	45Hz - 1kHz	45Hz - 3kHz	45Hz - 10kHz
Transistor	Yes	-	-	-	-
NCV	Yes	-	-	-	-
Peak Value	-	-	-	-	Yes
RS232	-	Yes	Yes	Yes	Yes
Analog Bar Graph	41 Segments	41 Segments	61 Segments	61 Segments	46 Segments
Standard Accessories	Battery, Test Lead, Multi-Purpose Socket, Instruction Manual	Battery, Test Lead, Multi-Purpose Socket, RS-232 Interface Cable, Software, Point Contact Temperature Probe, Instruction Manual		Battery, Test Lead, Multi-Purpose Socket, RS-232 Interface Cable, Software, Instruction Manual	



Digital Multimeters



Part Number Table

Description	Part Number
Digital Multimeter, Handheld	72-2605
Digital Multimeter, Handheld	72-10405
Digital Multimeter, Handheld	72-2610
True RMS Digital Multimeter, Handheld	72-10410
True RMS Digital Multimeter, Handheld	72-10415

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.



Weatherproof Tool Case with Foam



Specifications

Case Material	: Polymer
Case Colour	: Yellow
External Dimensions - Metric (W × D × H)	: 470mm × 357mm × 176mm
External Dimensions - Imperial (W × D × H)	: 18.5" × 14.06" × 6.93"
Internal Dimensions - Metric (W × D × H)	: 430mm × 285mm × 165mm
Internal Dimensions - Imperial (W × D × H)	: 16.93" × 11.22" × 6.5"

Part Number Table

Description	Part Number
Weatherproof Tool Case with Foam, Polymer, Yellow	22-24116

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

