



## Main

Range of product	OsiSense XU
Series name	Application
Electronic sensor type	Photo-electric sensor
Sensor name	XUY
Sensor design	Fork
Detection system	Thru beam
Emission	Infrared, continuous
Passage width	2 mm
Passage depth	40 mm
Material	Metal
Supply circuit type	DC
Wiring technique	4-wire
Discrete output type	PNP/NPN
Electrical connection	1 male connector M8, 4 pins
Product specific application	Control of tools travel Detection of marks on a translucent film Detection of sheets overlapping Detection on a labelling machine Lateral shift control of a belt Lift cage position control
[Sn] nominal sensing distance	2 mm

## Complementary

Enclosure material	Painted aluminium strong housing
Type of output signal	Discrete
Output type	Solid state
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Supply voltage limits	10...30 V DC
Switching capacity in mA	100 mA (overload and short-circuit protection)
Switching frequency	10 kHz
Voltage drop	< 1 V at 10 mA (closed state) < 2 V at 100 mA (closed state)
Current consumption	40 mA (no-load)

Time response	30 $\mu$ s
Delay recovery	30 $\mu$ s
Depth	12 mm
Length	60 mm
Width	40 mm

## Environment

Product certifications	CE cULus
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-20...80 °C
Immunity to ambient light	<= 3000 lux with incandescent bulb <= 3000 lux with natural light
IP degree of protection	IP65 conforming to IEC 60529

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0704 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

## Contractual warranty

Warranty period	18 months
-----------------	-----------